



DOL-0804-G05MNI

Plug connectors and cables

ACCESSORIES

SICK
Sensor Intelligence.



Ordering information

Type	Part no.
DOL-0804-G05MNI	6059194

Other models and accessories → www.sick.com/Plug_connectors_and_cables

Detailed technical data

Technical specifications

Accessory group	Plug connectors and cables
Accessory family	Connecting cables with female connector
Connection type head A	Female connector, M8, 4-pin, straight
Connection type head B	Cable
Connection type	Flying leads
Connector material	PUR
Connector color	Blue
Locking nut material	Stainless steel (V4A/1.4404)
Cable	5 m, 4-wire, unshielded, PVC
Jacket material	PVC
Jacket color	Gray
Cable diameter	4.8 mm
Conductor cross-section	0.25 mm ²
Shielding	Unshielded
Bending radius	> 5 x cable diameter (stationary position), > 10 x cable diameter (flexible use)
Tightening torque	0.4 Nm
Reference voltage	≤ 30 V
Rated impulse voltage	0.8 kV
Current loading	4 A
Application	Hygienic systems
Note	This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind. ¹⁾ CYJV.E335179 ²⁾
Authorizations	Ecolab, CSA approval, UL
Ambient operating temperature	-25 °C ... +85 °C, female connector -30 °C ... +80 °C, stationary position -5 °C ... +80 °C, flexible use
Enclosure rating	IP65 IP67 IP69K

¹⁾ Tested detergent: P3-topactive DES, P3-topax 19, P3-topax 56, P3-topax 66 and P3-topax 99; Insulating material group: Cat I.

²⁾ Insulating material group: Cat I.

Classifications

ECI@ss 5.0	19030312
ECI@ss 5.1.4	19030312
ECI@ss 6.0	27060304
ECI@ss 6.2	27060304
ECI@ss 7.0	27060304
ECI@ss 8.0	27060304
ECI@ss 8.1	27060304
ECI@ss 9.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
UNSPSC 16.0901	26121604

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com