D Sub Connector Kits

multicomp PRO

RoHS Compliant





Backshell Kit Includes

- Backshell Halves
- 4-40 Thumbscrews
- · Housing Screws & Nuts
- · Metal Strain Relief
- Set of compression inserts various sizes
 Diameters: 4mm(.157"), 5mm(.197"), 7mm (.276"), 9mm (.351")

Specifications

Plastic : ABS UL 94-HB Rated

Plating : Nickel Plated


Jackscrews : Steel-Zinc Plated


M3 Hoodscrews : Steel-Zinc Plated

Compression Inserts : ABS UL 94-HB Rated

M3 Nuts : Steel-Zinc Plated

Operating Temperature : -55° to +110°C





Dimessions (mm/in)						
Size	Α	В	С	D		
9	31.5	24.99	40.5	15		
	1.24	0.984	1.594	0.591		
15	40	33.32	40.5	15		
	1. <u>5</u> 7.5	1. <u>31.2</u>	1. <u>59</u> .4	0.58ქ		
25	5 4 ⁰²	47.04	4 ⁺ 0.02 49.5	₹ <u>6</u> 02		
	2.126	1.852	1.949	0.591		

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



D Sub Connector Kits



Specifications

 $\begin{array}{lll} \mbox{Rated Voltage} & : 250 \mbox{V} \\ \mbox{Rated Current} & : 5 \mbox{MP} \\ \mbox{Contact Resistance} & : 20 \mbox{M} \mbox{Max}. \end{array}$

Insulation Resistance : 1000MΩ Min. at 500V DC


Withstand Voltage : 500V/minute
Temperature Range : -55°C to +105°C


Materinal


Plastic : PBT+30% G.F (UL94V-0) Black

Terminal : Brass, Tin-Gold Plated

Spcc Shell : Spcc front shell is ni plated back shell is tin plated







Dimessions (mm)						
Pin	Α	В	C	D		
9	30.81	24.99	16.92	19.28		
15	39.25	33.32	25.25	27.75		
25	53.03	47.04	38.96	41.3		

Dimensions: Millimetres

Part Number Table

Description		
D-Sub Connector Kit with Metallised Plastic Backshell, 9 Pos Male Stamped and Formed Connector	MP010161	
D-Sub Connector Kit with Metallised Plastic Backshell, 15 Pos Male Stamped and Formed Connector	MP010163	
D-Sub Connector Kit with Metallised Plastic Backshell, 25 Pos 25 Pos Male Stamped and Formed Connector	MP010165	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

