

## SDUC offset cemented carbide boring bar, positive, right

for longitudinal and copy turning with DC indexable insert with holder

**ATORN**<sup>®</sup>



### Application

For longitudinal and copy turning with DC indexable insert, 55°

### Version

- precision-manufactured **solid carbide** boring bar, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

### Advantage

- slim contour, optimised for copy turning work
- Positive body geometry ensures low cutting forces

<b>Art. No.</b>	<b>17827 672</b>
<b>ISO name</b>	E0408-SDUC R/L 04-AX
<b>Min. bore diameter</b>	5.6 mm
<b>Shaft diameter</b>	8 mm
<b>Clearance length</b>	26 mm
<b>Length</b>	57 mm
<b>Programming size</b>	3 mm
<b>Plate height</b>	1.5 mm
<b>Suitable for indexable inserts</b>	DC.. 04..
<b>Tool design</b>	Right

### EAN-Code

4050293562194