

Micrometer

With disc measuring faces, non-rotating spindle

Mitutoyo

Application:

For measuring tooth span on cogs, for recesses, groove distances etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- Non-rotating measuring spindle
- Measurable division range: module 0.5–6

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box and adjustment wrench



Art. no.	32116 664
Brand	MITUTOYO
Manufacturer Part Number	169-205-10
Min./max. length measuring range	50-75 mm
Vernier scale	0.01 mm
Measuring surface diameter	20 mm
Measuring spindle increments	0.5 mm
Bracket depth	49 mm
Spindle clamping	No
Error limit	6 µm
Display	Nonius
Min./max. measurement force	5-10 N
Calibration Group	D
Gross Weight	0.315 kg
Product Group	3MA

EAN

4946368847597