

Boring bar holder, shape E2

For turning tools with cylindrical shanks

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply



Art. no.	22778 122
Brand	ORION
Manufacturer Part Number	22778122
VDI mount diameter	40 mm
Clamping diameter	40 mm
Length	22 mm
Outer diameter	83 mm
Projecting length	90 mm
Gross Weight	3.408 kg
Product Group	2AC

EAN

4053625465200

