

Pull clamps (under tension)



Application:

For quick and secure clamping on machine tables and appliances.

Execution:

- With elbow lever transmission
- Galvanised and passivated
- Hooks and clamping sleeve tempered
- Rivet made of stainless steel
- Case-hardened and lubricated bearing bushes
- With red oil-resistant plastic handle
- The self-locking feature in the clamped position prevents the clamp from opening as a result of machining forces.



Art. no.	26219 110
Brand	AMF
Manufacturer Part Number	94524
Size	1
Max. tensile force	2 kN
Min./max. clamping width	16-23 mm
Max. adjustment range	8 mm
Min./max. clamping width 2	35-42 mm
Height	111 mm
Bore diameter	4.5 mm
Bracket diameter	5.3 mm
Length	88 mm
Min./max. distance between baseplate fastenings	16.5-23.5 mm
Min./max. boom arm length	35-42.5 mm
Length 2	31 mm
Counterholder weight	22.7 mm
Min./max. elongated hole spacing	25.5-30.5 mm
Overall height of lower handle 2	34.5 mm
Distance between centre and drill hole 2	6 mm
Hole distance	19 mm
Width	40 mm
Boom arm length	62.6 mm
Radius	4.5 mm
Boom arm length 2	45 mm
Gross Weight	0.107 kg
Product Group	260

EAN

4020772094522