## **ZB4BV013**

Head for pilot light, Harmony XB4, metal, white, 22mm, universal LED, plain lens





#### Main

| Range of Product                | Harmony XB4           |
|---------------------------------|-----------------------|
| Product or Component<br>Type    | Head for pilot light  |
| Product Compatibility           | Universal LED         |
| Device short name               | ZB4                   |
| Bezel material                  | Chromium plated metal |
| Mounting diameter               | 0.87 in (22 mm)       |
| Sale per indivisible quantity   | 1                     |
| Head type                       | Standard              |
| Shape of signaling unit head    | Round                 |
| Cap/operator or lens colour     | White                 |
| Operator additional information | With plain lens       |

#### Complementary

| CAD overall width                  | 1.14 in (29 mm)   |  |
|------------------------------------|---|--|
| CAD overall height                 | 1.14 in (29 mm)   |  |
| CAD overall depth                  | 1.18 in (30 mm)   |  |
| Net Weight                         | 0.06 lb(US) (0.026 kg)  |  |
| Resistance to high pressure washer | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m                                 |  |
| Electrical composition code        | P1 front mounting integral LED P2 front mounting integral LED and transformer |  |
| Device presentation                | Basic element   |  |

#### **Environment**

| TH   |
|--|
| -40158 °F (-4070 °C)   |
| -40158 °F (-4070 °C)   |
| Class I IEC 60536  |
| IP66 IEC 60529<br>IP67<br>IP69<br>IP69K  |
| NEMA 13<br>NEMA 4X   |
| IK06 IEC 50102   |
| EN/IEC 60947-5-4 EN/IEC 60947-5-5 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14 EN/IEC 60947-1 JIS C8201-5-1 JIS C8201-1 |
| 5 gn 2500 Hz)IEC 60068-2-6   |
| 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27    |
|  |

### Ordering and shipping details

| Category          | 22468-PUSHBUTTONS,22MM(METAL) NEW |
|-------------------|-----------------------------------|
| Discount Schedule | CS2                               |
| GTIN              | 3389110123234                     |
| Returnability     | Yes                               |
| Country of origin | FR                                |

#### Packing Units

| - coming office              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 1.73 in (4.400 cm)      |
| Package 1 Width              | 1.34 in (3.400 cm)      |
| Package 1 Length             | 2.13 in (5.400 cm)      |
| Package 1 Weight             | 0.95 oz (27.000 g)      |
| Unit Type of Package 2       | BB1                     |
| Number of Units in Package 2 | 5                       |
| Package 2 Height             | 1.73 in (4.400 cm)      |
| Package 2 Width              | 1.34 in (3.400 cm)      |
| Package 2 Length             | 10.43 in (26.500 cm)    |
| Package 2 Weight             | 4.87 oz (138.000 g)     |
| Unit Type of Package 3       | S03                     |
| Number of Units in Package 3 | 300                     |
| Package 3 Height             | 11.81 in (30.000 cm)    |
| Package 3 Width              | 11.81 in (30.000 cm)    |
| Package 3 Length             | 15.75 in (40.000 cm)    |
| Package 3 Weight             | 19.30 lb(US) (8.755 kg) |
|                              |                         |

#### Offer Sustainability

| Sustainable offer status   | Green Premium product                                      |
|----------------------------|--|
| REACh Regulation           | <sup>™</sup> REACh Declaration                             |
| REACh free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      | ☑ China RoHS Declaration                                   |
| RoHS exemption information | ₫Yes   |
| Environmental Disclosure   | Product Environmental Profile                              |
| Circularity Profile        | ☑ End Of Life Information                                  |


#### Contractual warranty

| Warranty  | 10 months |
|-----------|-----------|
| vvarranty | 18 months |
|           |           |

# Product data sheet Dimensions Drawings

# **ZB4BV013**

#### **Dimensions**




#### Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

# Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board Connection by Faston Connectors Connection by Faston Connectors

- (1) Diameter on finished panel or support
- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm  $_0$   $^{+0.4}$  / 0.88 in.  $_0$   $^{+0.016}$ )
- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.

#### Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

#### Panel Cut-outs (Viewed from Installer's Side)




A: 30 mm min. / 1.18 in. min.

B: 40 mm min. / 1.57 in. min.


Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. B: 40 mm min.

Dimensions in in.



A: 1.18 in. min. B: 1.57 in. min.


#### General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in: T1 + T2 = 0.3 mm max.

#### **Installation Precautions**

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB4 BZ009: ± 2 30' (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
  - o every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - o with each selector switch head (ZB4 BD•, ZB4 BJ•, ZB4 BG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Panel
- (2) Printed circuit board

#### Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ 01•
- 38 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ 01•

Dimensions An + 18.1 relate to the Ø 2.4 mm  $\pm$  0.05 / 0.09 in.  $\pm$  0.002 holes for centring adapter ZBZ 01•.

# **ZB4BV013**

| Electrical Composition Corresponding to Codes P1, P3, PF1, PR1 and PF2 |
|--|
| Light block  |
|  |
|  |
| Electrical Composition Corresponding to Codes M6 and P2                |
|  |
| -8-  |
| Legend   |
| Single contact   |
|  |
| Double contact   |
|  |
|  |
| Light block  |
|  |
|  |
| Possible location  |
|  |
|  |