







Dimension drawing



D 9025

Cable junction box

- · for normal environment and protected outdoor
- with terminals

Approval mark

rated connecting capacity

conductor material:

Polarity conductor cross section

rated insulation voltage

degree of protection:

degree of protection:

material: colour:

cable entry

sealing range

in accordance with



Cu

5-pole, per pole sol 6 x 1,5 mm² sol 4 x 2,5 mm² sol 3 x 4 mm² mm² AC/DC 690 V

IP 55 (ESM)

(refer to index LES) IP 65

thermoplastic grey RAL 7035

included 4 ESM 20

Ø 6-13 mm mm IEC 60,670-22

| Operating and ambient conditions | |
|--|---|
| Application area | Suitable for indoor installation and outdoor installation, protected against weather |
| Resistant to occasional cleaning procedures (direct jet) | without additives, water pressure: max. 100 bar, water temperature: max. 80° C, |
| ambient temperature | distance => 0,15 m, in accordance with the requirements IP 69K, enclosure and cable glands at least IP 65 Average value over 24 hours + 35° C Maximum value + 40° C Minimum value - 25° C |
| Relative humidity Fire protection in the event of internal faults | 50% at 40° C short-time 100% at 25° C Demands placed on electrical devices from standards and laws Minimum requirements - Glow wire test in accordance with IEC 60 695-2-11: - 650°C for boxes and cable glands - 850°C for parts of insulating material necessary to retain |
| Fire protection in the event of specific risks or hazards | current carrying parts in position Demands placed on electrical installations and devices in areas and facilities subject to fire risk, e.g. DIN VDE 0100 Part 482, official regulations, VdS directives Minimum requirements - Glow wire test to IEC 60 695-2-11: - 850°C for boxes and |
| Burning behaviour | cable glands - 850°C for cavity wall installation - Use of fire resistant cables Glow wire test IEC 60 695-2-11: 750°C UL Subject 94 V-2 |
| degree of protection against mechanical load | flame resistant self-extinguishing IK07 (2 Joule) |
| Toxic behaviour | halogen-free silicone-free "halogen-free" in accordance with the examination of the cables and insulated wires - corrosiveness of fumes - as per IEC 754-2 |
| Note: | To material properties see technical data. |