



Figure similar

FILTER FAN AIR FLOW FREE AIR 25 M3 PER H CUT
OUT 92X92 MM 230 V AC RAL 7032 INPUT POWER
12W DEGREE OF PROTECTION IP 54 ACCURACY
CLASS 2

Model		
product brand name		SIVACON
Product designation		filter fan
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
A-rated sound power level / maximum	dB	30
Active power consumption / Rated value	W	12
Cutout width	mm	92
Cutout height	mm	92
Operating period	h	37 500
Operating temperature / minimum	°C	-10
Cooling capacity / at 35 °C	W	4.7
Rotor speed / at 50 Hz / Rated value	1/min	2 700
Rotor speed / at 60 Hz / Rated value	1/min	3 200
Protection class		
Protection class IP		IP54
Electricity		
Consumed current / minimum	A	0.07
Main circuit		
Operating voltage		
<ul style="list-style-type: none"> with AC / at 50 Hz / Rated value / maximum 	V	230
<ul style="list-style-type: none"> with AC / at 60 Hz / Rated value / maximum 	V	230

Appearance

Color		RAL 7032
-------	--	----------

Product details

Product component / Fan		No
-------------------------	--	----

Number

Number of ventilators		1
-----------------------	--	---

Mechanical Design

Height	mm	105
--------	----	-----

Width	mm	105
-------	----	-----

Depth	mm	59.5
-------	----	------

Mounting type		snap-on mounting
---------------	--	------------------

Mounting type		No
• 19-inch installation		Yes
• wall mounting		

Material		plastic
----------	--	---------

Certificates

Equipment marking		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64232LV10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64232LV10/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR64232LV10

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015