

XBee® 868LP for Europe

Low-Power RF Module for Europe

RF module family operates in the 863-870 MHz range utilizing 30 channels to deliver superior throughput performance and interference immunity at 868 MHz.



Overview

The XBee 868LP module was designed to provide a high-performance, low-power module at an extremely competitive price point. The XBee 868LP module can run either a proprietary DigiMesh® or point-to-multipoint networking protocol utilizing a low-power Energy Micro microcontroller and an Analog Devices ADF7023 transceiver, which offers industry-leading interference blocking. The XBee 868LP operates between 863-870 MHz, making it deployable in several regions throughout the world including approved European countries and India by utilizing a software selectable channel masking feature.

The XBee 868LP is also the industry's first RF module using 868 MHz and surrounding frequencies for LBT + AFA (Listen Before Talk and Adaptive Frequency Agility). This virtually eliminates interference by listening to the radio environment before any transmission starts, and automatically shifting to a new channel when interference is detected. This patent-pending frequency scan occurs automatically and in a matter of microseconds so as not to impact performance.

The programmable version of the XBee 868LP module makes customizing wireless applications easy. Programming directly on the module eliminates the need for a separate host processor. Because the wireless software is isolated, applications can be developed with no risk to RF performance, security or additional certifications.

Related Products



Gateways




Development Kits



Modules

Application Highlight






Features/Benefits

- Industry's first RF module to utilize LBT + AFA for interference immunity
- Modules can operate in DigiMesh or point-to-multipoint wireless networking topologies
- Programmable versions of the XBee 868LP enable custom application development
 - 8-bit Freescale™ S08 microprocessor brings custom intelligence to the module
 - XBee-specific CodeWarrior® development tools for easy programming
- Pin-compatible with XBee® ZB SMT versions
- RF throughput up to 50 Kbps



Hardware		
Processor	ADF7023 transceiver, Cortex™-M3 EFM32G230 @ 32 MHz	
Frequency Band	863 MHz to 870 MHz	
Antenna Options	U.FL, RF pad, PCB (PCB antenna only approved with 10 Kbps data rate)	
Performance		
RF Data Rate	10 Kbps or 80 Kbps	
Indoor/Urban Range	Up to 500 ft (150 m) w/2.1 dBi antenna, up to 250 ft (75 m) w/PCB embedded antenna	
Outdoor/Line-Of-Sight Range	Up to 2.5 miles (4 km) w/2.1 dBi antenna, up to 0.6 miles (1 km) w/PCB embedded antenna	
Transmit Power	Up to 12 dBm (16 mW), software selectable	
Receiver Sensitivity	-101 dBm @ 80 Kbps, -106 dBm @ 10 Kbps	
Features		
I/O	13	
Analog Inputs	4 channels 10-bit	
Operating Temperature	-40° C to +85° C	
Networking Topologies	DigiMesh®, Repeater, Point-to-point, Point-to-multipoint, Peer-to-peer	
Programmability		
Memory	N/A	32 KB Flash / 2 KB RAM
CPU/Clock Speed	N/A	HCS08 / Up to 50.33 MHz
Power		
Supply Voltage	2.7- 3.6 VDC	
Transmit Current	48 mA	62 mA
Receive Current	27 mA	41 mA
Sleep Current	1.7 uA	2.3 uA
Regulatory Approvals		
ETSI (Europe)	CE	
RoHS	Yes	



Visit www.digi.com for part numbers.

DIGI SERVICE AND SUPPORT - You can purchase with confidence knowing that Digi is here to support you with expert technical support and a strong one-year warranty. www.digi.com/support

91001811
A4/113

**Digi International
Worldwide HQ**

877-912-3444
952-912-3444

**Digi International
France**

+33-1-55-61-98-98
www.digi.fr

**Digi International
Japan**

+81-3-5428-0261
www.digi-intl.co.jp

**Digi International
India**

+91-80-4287-9887

**Digi International
Singapore**

+65-6213-5380

**Digi International
China**

+86-21-5150-6898
www.digi.cn

BUY ONLINE • www.digi.com

© 2011-2012 Digi International Inc. All rights reserved. Digi, Digi International, the Digi logo, Digi Mesh and XBee are trademarks or registered trademarks of Digi International Inc. in the United States and other countries worldwide. All other trademarks are the property of their respective owners. All information provided is subject to change without notice.

info@digi.com

