## Reflex Sensor

for Roller Conveyor Systems


# **OPT1503**

Part Number



- Energy savings thanks to EcoMode
- Optimized performance
- Quick wiring
- Scaled switching distance adjuster
- Time-saving installation with fast-clip mounting system

These sensors have been specially designed for use in accumulation roller conveyors. Their compact design allows for installation between rollers below the transport level. High-precision background suppression makes it possible to reliably detect even black objects at up to 900 mm. The scaled switching-distance adjuster assures quick and simple adjustment to the desired distance. Thanks to the innovative fast-clip mounting system and quick wiring, the sensor are installed and ready for use in no time flat.



#### **Technical Data**


ecnnical Data	
Optical Data	000 mm
Range	900 mm
Switching Hysteresis	
Light Source	Infrared Light
Wavelength	860 nm
Service Life (T = +25 °C)	100000 h
Risk Group (EN 62471)	1
Max. Ambient Light	90000 Lux
Opening Angle	3 °
Electrical Data	
Supply Voltage	2327,8 V DC
Current Consumption Sensor (Ub = 24 V)	< 16 mA
EcoMode	yes
Switching Frequency	100 Hz
Response Time	5 ms
Temperature Drift	< 5 %
Temperature Range	-4060 °C
Number of Switching Outputs	1
Switching Output Voltage Drop	< 0,9 V
PNP Switching Output/Switching Current	200 mA
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Overload Protection	yes
Logic	yes
Single Discharge	yes
Block Forwarding	yes
Solenoid Valve	yes
Protection Class	III
Mechanical Data	
Setting Method	Potentiometer
Housing Material	Plastic
Degree of Protection	IP65
Connection	M12 × 1; 4-pin
Cable Length	100 cm
Pneumatic Solenoid Valve Unit	
Valve no.	K03
Supply Voltage Valve	21,626,4 V
Current Consumption Valve	42 mA
Valve temperature range	-1055 °C
Operating Pressure	08 bar
Nominal Width	0.9 mm
Nominal flow rate 1 -> 2	22 NL/min
Nominal flow rate 2 -> 3	25 NL/min
Supply-Line Connector Pipe	2× 8×1
Working-Line Connector Pipe	4×1
Valve function	3/2-Way
Switching function	NO
	INU
PNP NC	
Connection Diagram No.	734
Control Panel No.	OP1
Suitable Connection Equipment No.	2 2s
Suitable Mounting Technology No.	421

#### **Complementary Products**

Adapter OPT70N, OPT70S, OPT70P

ZPTX001 Quick Mount






### Ctrl. Panel



- 05 = Switching Distance Adjuster
- 30 = Switching Status/Contamination Warning



Legen	nd		PT	Platinum measuring resistor	ENARS42	₂ Encoder A/Ā (TTL)	
+	Supply Voltage +		nc	not connected	ENBR542	Encoder B/B (TTL)	
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B	
Α	Switching Output	(NO)	W	Trigger Input	Amin	Digital output MIN	
Ā	Switching Output	(NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX	
V	Contamination/Error Output	(NO)	0	Analog Output	Аок	Digital output OK	
V	Contamination/Error Output	(NC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input		Awv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance	
S	Shielding		b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path		SY	Synchronization	Wire C	e Colors according to DIN IEC 757	
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black	
RDY	Ready		E+	Receiver-Line	BN	Brown	
GND	Ground		S+	Emitter-Line	RD	Red	
CL	Clock		<b>±</b>	Grounding	OG	Orange	
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow	
•	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue	
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey	
Signal	Signal Output		Mag	Magnet activation	WH	White	
BI_D+/-	Ethernet Gigabit bidirect, data	line (A-D)	RES	Input confirmation	PK	Pink	
	Encoder 0-pulse 0-0 (TTL)	, ,	EDM	Contactor Monitoring	GNYE	Green/Yellow	

## **Switching Distance Deviation**

Typical characteristic curve based on white, 90 % remission

