

SDJC clamp holder with internal cooling, positive

for longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

for longitudinal and copy turning with DC indexable insert, 55°

Version

- precision-manufactured steel support with high-performance internal cooling system, nickel-plated, hardened, type D, working angle 93°, tip angle 55°, clearance angle 7°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable work
- streamlined geometry, optimised for contour lathe work
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing



Art. no.	17835 715
ISO name	SDJC R/L 2020 K11 IK G1/8
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	20.5 mm
Programming size	25 mm
Suitable for indexable inserts	DC.. 11T3..
Tool design	Left
DIN	4983

EAN-Code

4050293566413