

## Manual forklift, manual hydraulic forklift truck

Carrying capacity 1000 kg

**hanhart**  
CHRONOGRAPHEN 1882

### Application:

Hand hydraulic stacker to lift and move palletised goods

### Version:

- Stable welded, torsion-proof sectional steel structure
- Safe position even under full load
- Hydraulic lifting by means of drawbar or pedal
- Manual lowering infinitely adjustable via handle
- Safety draw bar with rubberised handle
- Hydraulic system with safety valve
- Hard chromium plated pressure piston
- With protective grating, fixed down to the bottom of the frame, against falling objects and for free sight to the front
- Quiet polyurethane rollers facilitate the work
- 2 large steering wheels with parking brakes, for optimum manoeuvring even in narrow spaces, ground clearance of fork arms 40 mm, allows bumps in the ground to be travelled over effortlessly, all forklift trucks comply both with the requirements of the regulations of the employers' liability insurance association of BGV-D27 and the Euronorm colour: RAL 5012, light blue, powder-coated



<b>Art. no.</b>	<b>50262 510</b>
<b>Load-carrying capacity</b>	1000 kg
<b>Length</b>	1705 mm
<b>Width</b>	755 mm
<b>Fork length</b>	1150 mm
<b>Fork arm width</b>	170 mm
<b>Fork, external distance</b>	550 mm
<b>Fork roller diameter</b>	83 mm
<b>Min. lift height</b>	90 mm
<b>Lift height</b>	1600 mm
<b>Stroke height per pedal movement</b>	20 mm
<b>Castor-wheel diameter</b>	150 mm
<b>Material of steering wheels</b>	Polyurethane
<b>Min. overall height</b>	1980 mm
<b>Max. overall height</b>	2080 mm
<b>Colour</b>	Light blue RAL 5012
<b>Surface</b>	Powder-coated
<b>Turning radius</b>	1400 mm
<b>With free stroke</b>	1440 mm
<b>Travel drive</b>	Manual
<b>Fork castor design</b>	Tandem

### EAN-Code

4260151120576