

## Spring balance with compressed air spiral hose, load capacity 0.5-3.0 kg

Type 7211, cable extraction 2500 mm

**AUTOSTAT**

### Application:

Particularly suited for compressed air tools with high air consumption.

### Execution:

- Larger load-bearing ranges
- Housing made of extremely shock-resistant special plastic
- Cable drum is made of non abrasive plastic
- Riveted load-bearing spring made from high-strength special steel
- Suspension with screw snap hook
- Cable feed limitation is impact absorbing and adjustable
- The load is attached via a safe screw snap hook
- Spiral hose: made of PU, 9 x 13 mm, colour yellow or 11 x 16 mm, colour blue, including straight inlets and outlets of 500 mm, operating pressure up to max. 10 bar, without compressed air connections
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, insulated suspension, shape-stabilised structure
- Working area: Cable extraction: 2500 mm

### Delivery:

Without compressed air connections and couplings, deliverable on request: with automatic locking



<b>Art. no.</b>	<b>77001 501</b>
<b>Brand</b>	AUTOSTAT
<b>Manufacturer Part Number</b>	77001501
<b>Min./max. load-carrying capacity</b>	0.5-2 kg
<b>Model</b>	7211/101
<b>Spring design</b>	Special mainspring
<b>Max. cable pull-out length</b>	2500 mm
<b>Adjustable cord length</b>	No
<b>Wire cable diameter</b>	2 mm
<b>Replaceable cord</b>	No
<b>Cord in-feed restriction</b>	Absorbs impacts, adjustable
<b>Material of cable drum</b>	Plastic
<b>With automatic locking</b>	No
<b>Connection thread</b>	Without
<b>Max. hose extension length</b>	2500 mm
<b>Inner hose diameter</b>	9 mm
<b>Outer diameter of hose</b>	13 mm
<b>Max. operating pressure</b>	10 bar
<b>Suspension type</b>	Freely rotating and pivot screw karabiner hook
<b>Load attachment</b>	Screw Karabiner hook
<b>Material of housing</b>	Plastic
<b>Housing height</b>	166.5 mm
<b>Housing width</b>	133 mm
<b>Housing thickness</b>	45 mm
<b>Height</b>	420 mm
<b>DIN</b>	15112
<b>Gross Weight</b>	1.720 kg
<b>Product Group</b>	772

### EAN

4039247878680

LET'S WORK TOGETHER.