

5747844-3 ✓ ACTIVE




AMPLIMITE

TE Internal #: 5747844-3

PCB D-Sub Connectors, Receptacle, Board-to-Board, 9 Position, 2.74 mm [.108 in] Centerline, 2 Row, Size 1, Round, Standard Profile, Right Angle

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Receptacle Assembly: Right Angle, Shell Size 1, 2.74mm



Connector & Housing Type: Receptacle

Connector System: Board-to-Board

Number of Positions: 9

Centerline (Pitch): 2.74 mm [.108 in]

Number of Rows: 2

[All D-Sub Receptacle Assembly: Right Angle, Shell Size 1, 2.74mm \(77\)](#)

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Grounding Indents | Without |
| Grounded | No |
| Grounding Straps | With |
| Footprint | 8.08 mm[.318 in] |
| Shell Type | Front Metal Shell |
| Connector & Housing Type | Receptacle |
| Connector System | Board-to-Board |
| D-Sub Shell Size | 1 |
| Sealable | No |
| Connector & Contact Terminates To | Printed Circuit Board |
| Product Type | Connector |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 9 |
|---------------------|---|



| | |
|-----------------------|-------------|
| Number of Rows | 2 |
| PCB Mount Orientation | Right Angle |
| Preloaded | Yes |

Body Features

| | |
|-------------------------|-----------------|
| Eyelet Material | Brass |
| Eyelet Plating Material | Tin |
| Plastic | No |
| Insert Material | Zinc |
| Connector Profile | Standard |
| Shell Plating Material | Tin |
| Shell Material | Steel |
| Post Size | .66 mm[.026 in] |

Contact Features

| | |
|---|-----------------|
| Contact Mating Area Plating Material | Gold Flash |
| PCB Contact Termination Area Plating Material | Tin |
| Contact Base Material | Phosphor Bronze |
| Contact Shape & Form | Round |
| Contact Current Rating (Max) | 6 A |

Termination Features

| | |
|---|-----------------------|
| Grounding Clips | Without |
| Termination Method to Printed Circuit Board | Through Hole - Solder |
| Termination Post Length | 3.18 mm[.125 in] |

Mechanical Attachment

| | |
|----------------------------------|-----------------|
| Threaded Insert Material | Zinc |
| Threaded Insert Plating Material | Clear Chromate |
| PCB Mount Alignment | With |
| Panel Mount Feature | Without |
| PCB Mount Retention | With |
| PCB Mount Retention Type | Boardlock |
| Mating Retention | With |
| Mating Retention Type | Threaded Insert |
| Connector Mounting Type | Board Mount |



| | |
|----------------------------|------------------|
| Boardlock Plating Material | Tin |
| Boardlock Material | Copper Alloy |
| Mounting Hole Diameter | 3.18 mm[.125 in] |

Housing Features

| | |
|--------------------|------------------|
| Centerline (Pitch) | 2.74 mm[.108 in] |
| Housing Material | Thermoplastic |
| Housing Color | Black |

Dimensions

| | |
|-----------------------------|------------------|
| Row-to-Row Spacing | 2.84 mm[.112 in] |
| PCB Thickness (Recommended) | 1.58 mm[.062 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

| | |
|--------------------|------|
| Packaging Method | Tray |
| Packaging Quantity | 130 |

Other

| | |
|---------|--|
| Comment | All receptacles are preloaded with size 20 DF posted socket contacts |
|---------|--|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 |

ppm.

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-747944-6
KIT, PLUG, 9P, HDE, SHLD ENCL SRE



TE Part # CAT-023-DPARS1274
D-Sub Plug Assembly: Standard, Right Angle, Shell Size 1, 2.74mm



TE Part # 2-745492-0
PLUG ASSY, 9P, HDE, MS



TE Part # 206509-1
SIZE 20 KEYING PLUG

Customers Also Bought



TE Part # 36954
PIDG SLTD 22-16COMM 22-18MIL 8



TE Part # 6364106-4
AMP-LATCH UNIVERSAL HEADERS



TE Part # 5555165-5
M/J, LPF, R/A, 6P/2C, TIN, BULK PKG



TE Part # 2118715-2
STD SHIELD COVER, CRS-16.90X16.90X2.00MM



TE Part # 1-2176329-7
CRGP 1210 220R 1%



TE Part # 2331372-1
DET SW4.7X3.8X2.3 GW VERT. NO AG RL



TE Part # 1-2176389-2
RQ 1206 140R 0.1% 10PPM 5K RL



TE Part # 202174-4
GUIDE SOC. ASSY. 104 CTR. FSTN

Documents

[Product Drawings](#)



09 MSFL RCPT RA 318 (IN,FM,BL)

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_5747844-3_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_5747844-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5747844-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Right-Angle Posted Connectors](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_5747844-3_02162018816_dmtec](#)

English

[MD_5747844-3_02162018816_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English