


A-series
SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Control voltage distribution**

Our tailored AAP potential distribution terminal blocks are ideal for surge current protection and central control voltage distribution. Meanwhile, our new maxGUARD range enables potential distribution with integrated electronic load monitoring in the smallest of installation spaces.

General ordering data

| | |
|------------|--|
| Type | SET AAP11 6/1.5/24C |
| Order No. | 2506370000 |
| Version | Modular distribution terminals, PUSH IN, 6 mm ² , 500 V, 41 A, Dark Beige |
| GTIN (EAN) | 4050118520750 |
| Qty. | 1 pc(s). |

A-series
SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|--------------------------|---------|-----------------|------------|
| Width | 49 mm | Width (inches) | 1.929 inch |
| Height | 85.5 mm | Height (inches) | 3.366 inch |
| Depth | 47 mm | Depth (inches) | 1.85 inch |
| Depth including DIN rail | 48 mm | Net weight | 107.855 g |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|--------------------------------|-------|---------------------------|------------|
| Material | Wemid | Colour | Dark Beige |
| Colour of operational elements | Red | UL 94 flammability rating | V-0 |

System specifications

| | | | |
|-------------------------------|----|-----------------------------------|-------|
| End cover plate required | No | Number of potentials | 2 |
| Number of levels | 1 | No. of clamping points per level | 50 |
| Number of potentials per tier | 2 | Levels cross-connected internally | No |
| PE connection | No | Mounting rail | TS 35 |
| N-function | No | PE function | No |
| PEN function | No | | |

Additional technical data

| | | | |
|---------------------|---------------|------------------|-------|
| Installation advice | Mounting rail | Open sides | right |
| Type of fixing | Snap-on | Type of mounting | TS 35 |

Conductors for clamping (additional connection)

| | | | |
|---|--------------|---|---------|
| Blade size, additional connection | 0.4 x 2.0 mm | Clamping range, further connection, max. | 1.5 mm |
| Clamping range, further connection, min. | 0.14 mm | Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 1 mm |
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min. | 0.5 mm | Conductor cross-section, flexible, further connection, min. | 0.5 mm |
| Connection direction | top | Connection type, additional connection | PUSH IN |
| Cross-section for connected wire, AWG, additional connection, max. | AWG 14 | Cross-section for connected wire, AWG, additional connection, min. | AWG 26 |
| Cross-section for connected wire, flexible, further connection, max. | 1.5 mm | Cross-section for connected wire, multi-core, further connection, max. | 1.5 mm |
| Cross-section for connected wire, multi-core, further connection, min. | 0.5 mm | Cross-section for connected wire, solid-core, further connection, max. | 1.5 mm |
| Cross-section for connected wire, solid-core, further connection, min. | 0.5 mm | Rated cross-section, further connection | 1.5 mm |
| Stripping length, additional connection | 8 mm | | |

A-series
SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|---------------------|
| Blade size | 1.0 x 5.5 mm | Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 6 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Connection direction | top |
| Gauge to IEC 60947-1 | A5 | Number of connections | 1 |
| Stripping length | 12 mm | Twin wire-end ferrules, max. | 1.5 mm ² |
| Twin wire-end ferrules, min. | 0.5 mm ² | Type of connection | PUSH IN |
| Wire connection cross section AWG, max. | AWG 8 | Wire connection cross section AWG, min. | AWG 22 |
| Wire connection cross section, finely stranded, max. | 6 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded, min. | 0.5 mm ² |
| Wire connection cross-section, solid core, max. | 6 mm ² | Wire connection cross-section, solid core, min. | 0.5 mm ² |

Rating data

| | | | |
|---------------------------------|----------------------------------|--|---------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated current | 41 A | Current at maximum wires | 41 A |
| Standards | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV | Pollution severity | 3 |
| Surge voltage category | III | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000897 | eClass 6.2 | 27-14-11-20 |
| eClass 9.1 | 27-14-11-20 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text technical data | Approval in progress |
| Instructions for accessories | All MultiMark variants (MM) = strip markers |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | DE PT0205 20180316 014 ISSUE01.pdf |
| Engineering Data | STEP |

**A-series
SET AAP11 6/1.5/24C**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Digital multimeters




Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard. In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|-------------------|----------------------------|------------|---------------|----------|
| ZUB MULTIMETER | 9205270000 | Multimeter | 4032248723522 | 1 pc(s). |

Blank



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data


| Type | Order No. | Version | GTIN (EAN) | Qty. |
|-----------------------------|----------------------------|--|---------------|------------|
| WS 10/8 PLUS MC NE WS | 1905950000 | WS, Terminal marker, 10 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, White | 4032248528103 | 420 pc(s). |

A-series SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

End brackets



Spring connection with tension clamp Technology

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|-----------|----------------------------|-----------------------|---------------|------------|
| ZEW 35 | 9540000000 | Z-series, End bracket | 4008190956264 | 20 pc(s). |
| ZEW 35 V0 | 1264170000 | Z-series, End bracket | 4050118137170 | 20 pc(s). |
| ZEW 35 GR | 1238040000 | Z-series, End bracket | 405011802440 | 120 pc(s). |

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|------------------------|----------------------------|---|---------------|------------|
| DEK 5/8 MC SDR | 1856750000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, To customer specification | 4032248400867 | 160 pc(s). |
| DEK 5/8 PLUS MC SDR | 1046370000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, To customer specification | 4032248782079 | 160 pc(s). |

A-series
SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories**ZQV 1.5N****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

| Type | Order No. | GTIN (EAN) | Qty. |
|-------------------|----------------------------|---------------|-----------|
| ZQV 1.5N/6 RD | 1985730000 | 4050118370454 | 20 pc(s). |
| ZQV 1.5N/8 RD | 1985770000 | 4050118370508 | 20 pc(s). |
| ZQV 1.5N/3 RD | 1985670000 | 4050118370348 | 60 pc(s). |
| ZQV 1.5N/50 RD | 1985820000 | 4050118370270 | 5 pc(s). |
| ZQV 1.5N/4 RD | 1985690000 | 4050118370515 | 60 pc(s). |
| ZQV 1.5N/9 RD | 1985790000 | 4050118370386 | 20 pc(s). |
| ZQV 1.5N/10 RD | 1985800000 | 4050118370393 | 20 pc(s). |
| ZQV 1.5N/2 RD | 1985650000 | 4050118370324 | 60 pc(s). |
| ZQV 1.5N/5 RD | 1985710000 | 4050118370256 | 20 pc(s). |
| ZQV 1.5N/7 RD | 1985750000 | 4050118370249 | 20 pc(s). |
| ZQV 1.5N/20 RD | 1985810000 | 4050118370355 | 20 pc(s). |

A-series SET AAP11 6/1.5/24C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|------------|----------------------------|---|---------------|------------|
| DEK 5/8 MC | 1856740000 | Dekafix, Terminal marker, | 4032248400850 | 800 pc(s). |
| NE WS | | 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, White | | |

End brackets



Spring connection with PUSH IN Technology

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|-------------|----------------------------|-----------------------|---------------|-----------|
| AEB 35 SC/1 | 1991920000 | A-series, End bracket | 4050118376722 | 50 pc(s). |
| AEB 35 SC/1 | 2475310000 | A-series, End bracket | 4050118487114 | 50 pc(s). |
| BK | | | | |


Data sheet

**A-series
SET AAP11 6/1.5/24C**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Custom printing



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with laser printer, PrintJet ADVANCED, plotter or MC-Mobilo is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| Type | Order No. | Version | GTIN (EAN) | Qty. |
|------------------------|----------------------------|---|------------------|--------|
| WS 10/8 PLUS MC SDR | 1906030000 | WS, Terminal marker, 10 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, To customer specification | 4032248528196 84 | pc(s). |