

Turbo USB 3.0 Flash Drive



64 GB 128 GB 256 GB

INTRODUCTION

Integral Turbo USB 3.0 Flash Drive is our fastest USB range ever. Experience rapid data transfer and super-fast backup with this premium drive.

FEATURES

- Integral's fastest flash drive range - less waiting as Turbo USB uses a premium high-performance chipset
 - Capless design; slide to open, protects USB connector when closed, no cap to loose
 - Fully compatible with USB 2.0 (USB 2.0 transfer speed)
 - Up to 390MB/s* Read / 95MB/s* Write (64GB)
 - Up to 400MB/s* Read / 200MB/s* Write (128GB)
 - Up to 400MB/s* Read / 300MB/s* Write (256GB)
- *Based on internal testing, performance may vary based on system configuration.

PRODUCT TYPE

USB Flash Drive

INTERFACE TYPE

SuperSpeed USB 3.0

INTERFACE CONNECTIVITY

1x SuperSpeed USB - 9 Pin USB Type A

COMPATIBILITY

Windows XP, Vista, 7, 8.1 and 10
Mac OS v10.0 or Later.
Linux v2.4.0 and above.

ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°C
Max Operating Temperature 70°C

COMPLIANT STANDARD

Plug and Play

	LENGTH	WIDTH	DEPTH	WEIGHT
PRODUCT	53mm	20mm	9mm	12g
PACKED	170mm	105mm	13mm	24g

CAPACITY	PART CODE	BARCODE (EAN)
64GB	INFD64GBTURBWH3.0	5055288436084
128GB	INFD128GBTURBWH3.0	5055288436091
256GB	INFD256GBTURBWH3.0	5055288436107

This device should not be used as your sole backup.
Product design and specification subject to change or modification without notice. E&OE.
All trademarks acknowledged.
2 year warranty
For warranty information please visit www.integralmemory.com/warranty