
DISCRETE SEMICONDUCTORS



Product specification Supersedes data of May 1996 1996 Sep 26



BY448

Product specification

FEATURES

- · Glass passivated
- High maximum operating temperature
- Low leakage current
- Excellent stability
- Available in ammo-pack.

APPLICATIONS

• Damper diode in high frequency horizontal deflection circuits up to 16 kHz.

LIMITING VALUES

Ti

In accordance with the Absolute Maximum Rating System (IEC 134).

	0				
SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V _{RSM}	non-repetitive peak reverse voltage		_	1650	V
V _{RRM}	repetitive peak reverse voltage		_	1650	V
V _R	continuous reverse voltage		_	1500	V
I _{FWM}	working peak forward current	T _{amb} = 50 °C; PCB mounting (see Fig 4); see Fig.2	_	4	A
I _{FRM}	repetitive peak forward current		_	8	A
I _{FSM}	non-repetitive peak forward current	t = 10 ms half sinewave; $T_j = T_{j max}$ prior to surge; $V_R = V_{RRMmax}$	_	30	A
T _{stg}	storage temperature		-65	+175	°C

ELECTRICAL CHARACTERISTICS

junction temperature

 $T_i = 25 \ ^{\circ}C$; unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MAX.	UNIT
V _F	forward voltage	$I_F = 3 \text{ A}; T_j = T_{j \text{ max}}; \text{ see Fig.} 3$	1.45	V
		I _F = 3 A; see Fig.3	1.60	V
I _R	reverse current	$V_R = V_{Rmax}; T_j = 150 \ ^\circ C$	150	μA
t _{rr}	reverse recovery time	when switched from $I_F = 0.5$ A to $I_R = 1$ A; measured at $I_R = 0.25$ A; see Fig.6	1	μs
t _{fr}	forward recovery time	when switched to $I_F = 4 \text{ A in 50 ns};$ $T_j = T_j _{max}$; see Fig.7	1	μs

DESCRIPTION

Rugged glass package, using a high temperature alloyed construction.

This package is hermetically sealed and fatigue free as coefficients of expansion of all used parts are matched.

-65

+150

°C



Fig.1 Simplified outline (SOD57) and symbol.

BY448

THERMAL CHARACTERISTICS


SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R _{th j-tp}	thermal resistance from junction to tie-point	lead length = 10 mm	46	K/W
R _{th j-a}	thermal resistance from junction to ambient	note 1	100	K/W
		mounted as shown in Fig.5	55	K/W

Note


1. Device mounted on an epoxy-glass printed-circuit board, 1.5 mm thick; thickness of Cu-layer ≥40 μm, see Fig.4. For more information please refer to the *"General Part of associated Handbook"*.


BY448

GRAPHICAL DATA



BY448






BY448


APPLICATION INFORMATION

For horizontal deflection circuits, two basic applications are shown in Figs 8 and 9.

The maximum allowable total power dissipation for the diode can be calculated from the thermal resistance $R_{th j-a}$ and the difference between $T_{j max}$ and $T_{amb max}$ in the application. The maximum I_{FWM} can then be taken from Fig.2.


The basic application waveforms in Fig.10 relate to the circuit in Fig.8. In the circuit in Fig.9 the forward conduction time of the diode is shorter, allowing a higher I_{FWM} (see Fig.2).





BY448

PACKAGE OUTLINE



DEFINITIONS

Data Sheet Status		
Objective specification	jective specification This data sheet contains target or goal specifications for product development.	
Preliminary specification	This data sheet contains preliminary data; supplementary data may be published later.	
Product specification	This data sheet contains final product specifications.	
Limiting values		
Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.		
Application information		
Where application information is given, it is advisory and does not form part of the specification.		

LIFE SUPPORT APPLICATIONS

These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips for any damages resulting from such improper use or sale.