

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : DOWSIL™ 744 RTV Sealant White
Product code : 06003938

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-
stance/Mixture : Adhesive, binding agents

1.3 Details of the supplier of the safety data sheet

Company : DOW CHEMICAL COMPANY LIMITED
STATION ROAD, BIRCH VALE, HIGH PEAK
DERBYSHIRE
England
SK22 1BR
UNITED KINGDOM

Telephone : +44 (0) 1663 746518

Telefax : +44 (0) 1663 746605

E-mail address of person
responsible for the SDS : SDSQuestion@dow.com

1.4 Emergency telephone number

24-Hour Emergency Contact : 0031 115 694 982

Local Emergency Contact : 00 31 115 69 4982

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

Precautionary statements : **Prevention:**
P271 Use only outdoors or in a well-ventilated area.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Additional Labelling

EUH210 Safety data sheet available on request.
EUH208 Contains Methyltrimethoxysilane. May produce an allergic reaction.

2.3 Other hazards

None known.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Chemical nature : Silicone elastomer

Hazardous components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
Methyltrimethoxysilane	1185-55-3 214-685-0 01-2119517436-40	Flam. Liq. 2; H225 Skin Sens. 1B; H317	>= 0.1 - < 1
Octamethylcyclotetrasiloxane	556-67-2 209-136-7 014-018-00-1 01-2119529238-36	Flam. Liq. 3; H226 Repr. 2; H361f Aquatic Chronic 4; H413	>= 0.1 - < 0.25

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention.
- In case of skin contact : In case of contact, immediately flush skin with soap and plenty of water.
Remove contaminated clothing and shoes.
Get medical attention.
Wash clothing before reuse.
Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention.
Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

Risks : May produce an allergic reaction.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical

Unsuitable extinguishing media : None known.

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.

Hazardous combustion products : Carbon oxides
Metal oxides
Formaldehyde
Silicon oxides

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Follow safe handling advice and personal protective equipment recommendations.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

6.2 Environmental precautions

Environmental precautions : Discharge into the environment must be avoided.
Prevent further leakage or spillage if safe to do so.
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use only with adequate ventilation.

Advice on safe handling : Do not swallow.
Avoid contact with eyes.
Avoid prolonged or repeated contact with skin.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store in accordance with the particular national regulations.

Advice on common storage : Do not store with the following product types:
Strong oxidizing agents

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

7.3 Specific end use(s)

Specific use(s) : These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Calcium carbonate treated with stearic acid	Not Assigned	TWA (inhalable dust)	10 mg/m ³	GB EH40
Further information	For the purposes of these limits, respirable dust and inhalable dust are those fractions of airborne dust which will be collected when sampling is undertaken in accordance with the methods described in MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust, The COSHH definition of a substance hazardous to health includes dust of any kind when present at a concentration in air equal to or greater than 10 mg.m ⁻³ 8-hour TWA of inhalable dust or 4 mg.m ⁻³ 8-hour TWA of respirable dust. This means that any dust will be subject to COSHH if people are exposed above these levels. Some dusts have been assigned specific WELs and exposure to these must comply with the appropriate limit., Most industrial dusts contain particles of a wide range of sizes. The behaviour, deposition and fate of any particular particle after entry into the human respiratory system and the body response that it elicits, depend on the nature and size of the particle. HSE distinguishes two size fractions for limit-setting purposes termed 'inhalable' and 'respirable'. Inhalable dust approximates to the fraction of airborne material that enters the nose and mouth during breathing and is therefore available for deposition in the respiratory tract. Respirable dust approximates to the fraction that penetrates to the gas exchange region of the lung. Fuller definitions and explanatory material are given in MDHS14/3., Where dusts contain components that have their own assigned WEL, all the relevant limits should be complied with., Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used			
		TWA (Respirable dust)	4 mg/m ³	GB EH40
Further information	For the purposes of these limits, respirable dust and inhalable dust are those fractions of airborne dust which will be collected when sampling is undertaken in accordance with the methods described in MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust, The COSHH definition of a substance hazardous to health includes dust of any kind when present at a concentration in air equal to or greater than 10 mg.m ⁻³ 8-hour TWA of inhalable dust or 4 mg.m ⁻³ 8-hour TWA of respirable dust. This means that any dust will be subject to COSHH if people are exposed above these levels. Some dusts have been assigned specific WELs and exposure to these must comply with the appropriate limit., Most industrial dusts contain particles of a wide range of sizes. The behaviour, deposition and fate			

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version
1.15

Revision Date:
07.02.2018

SDS Number:
837107-00016

Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

	of any particular particle after entry into the human respiratory system and the body response that it elicits, depend on the nature and size of the particle. HSE distinguishes two size fractions for limit-setting purposes termed 'inhalable' and 'respirable'. Inhalable dust approximates to the fraction of airborne material that enters the nose and mouth during breathing and is therefore available for deposition in the respiratory tract. Respirable dust approximates to the fraction that penetrates to the gas exchange region of the lung. Fuller definitions and explanatory material are given in MDHS14/3., Where dusts contain components that have their own assigned WEL, all the relevant limits should be complied with., Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used			
Methyltrimethoxysilane	1185-55-3	TWA	7.5 ppm	DCC OEL
Octamethylcyclotetrasiloxane	556-67-2	TWA	10 ppm	US WEEL

These substance(s) are inextricably bound in the product and therefore do not contribute to a dust inhalation hazard.

Calcium carbonate treated with stearic acid

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value	
Methyltrimethoxysilane	Workers	Skin contact	Acute systemic effects	0.38 mg/kg bw/day	
	Workers	Inhalation	Acute systemic effects	25.6 mg/m3	
	Workers	Skin contact	Long-term systemic effects	0.38 mg/kg bw/day	
	Workers	Inhalation	Long-term systemic effects	25.6 mg/m3	
	Consumers	Skin contact	Acute systemic effects	0.3 mg/kg bw/day	
	Consumers	Inhalation	Acute systemic effects	6.25 mg/m3	
	Consumers	Ingestion	Long-term systemic effects	0.26 mg/kg bw/day	
	Consumers	Skin contact	Long-term systemic effects	0.3 mg/kg bw/day	
	Consumers	Inhalation	Long-term systemic effects	6.25 mg/m3	
	Consumers	Ingestion	Acute systemic effects	0.26 mg/kg bw/day	
	Octamethylcyclotetrasiloxane	Workers	Inhalation	Acute systemic effects	73 mg/m3
		Workers	Inhalation	Acute local effects	73 mg/m3
Workers		Inhalation	Long-term systemic effects	73 mg/m3	
Workers		Inhalation	Long-term local effects	73 mg/m3	
Consumers		Inhalation	Acute systemic effects	13 mg/m3	

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

	Consumers	Inhalation	Acute local effects	13 mg/m ³
	Consumers	Inhalation	Long-term systemic effects	13 mg/m ³
	Consumers	Inhalation	Long-term local effects	13 mg/m ³
	Consumers	Ingestion	Acute systemic effects	3.7 mg/kg bw/day
	Consumers	Ingestion	Long-term systemic effects	3.7 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
Methyltrimethoxysilane	Fresh water	≥ 1.3 mg/l
	Marine water	≥ 0.13 mg/l
	Fresh water sediment	≥ 1.1 mg/kg
	Marine sediment	≥ 0.11 mg/kg
	Soil	≥ 0.17 mg/kg
	Sewage treatment plant	> 6.9 mg/l
	Octamethylcyclotetrasiloxane	Fresh water
Marine water		0.000044 mg/l
Fresh water sediment		0.64 mg/kg
Marine sediment		0.064 mg/kg
Soil		0.13 mg/kg
Sewage treatment plant		> 10 mg/l

8.2 Exposure controls

Engineering measures

Processing may form hazardous compounds (see section 10).
Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye protection : Wear the following personal protective equipment:
Safety glasses

Hand protection
Material : Chemical-resistant gloves

Remarks : For prolonged or repeated contact use protective gloves.
Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. Breakthrough time is not

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

determined for the product. Change gloves often! For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

- Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).
- Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.
- Filter type : Organic vapour type (A)
-

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

- Appearance : paste
- Colour : white
- Odour : No data available
- Odour Threshold : No data available
- pH : Not applicable
- Melting point/freezing point : No data available
- Initial boiling point and boiling range : Not applicable
- Flash point : > 100 °C
Method: closed cup
- Evaporation rate : Not applicable
- Flammability (solid, gas) : Not classified as a flammability hazard
- Upper explosion limit / Upper flammability limit : No data available
- Lower explosion limit / Lower flammability limit : No data available
- Vapour pressure : Not applicable
- Relative vapour density : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Relative density : 1.39

Solubility(ies)
Water solubility : No data available

Partition coefficient: n-octanol/water : No data available

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, dynamic : Not applicable

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

9.2 Other information

Molecular weight : No data available

Particle size : No data available

Self-ignition : The substance or mixture is not classified as pyrophoric. The substance or mixture is not classified as self heating.

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : Use at elevated temperatures may form highly hazardous compounds.
Can react with strong oxidizing agents.
Methyl alcohol is formed upon contact with water or humid air.
Hazardous decomposition products will be formed at elevated temperatures.

10.4 Conditions to avoid

Conditions to avoid : None known.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

10.6 Hazardous decomposition products

Thermal decomposition : Formaldehyde

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Information on likely routes of exposure : Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Acute oral toxicity : LD50 (Rat): 12.3 ml/kg
Assessment: The substance or mixture has no acute oral toxicity
Remarks: Information taken from reference works and the literature.

Acute inhalation toxicity : LC50 (Rat): > 42.1 mg/l
Exposure time: 6 h
Test atmosphere: vapour
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: On basis of test data.

Acute dermal toxicity : LD50 (Rabbit): > 9,500 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: On basis of test data.

Octamethylcyclotetrasiloxane:

Acute oral toxicity : LD50 (Rat): > 4,800 mg/kg
Assessment: The substance or mixture has no acute oral toxicity
Remarks: On basis of test data.

Acute inhalation toxicity : LC50 (Rat): 2975 ppm
Exposure time: 4 h
Test atmosphere: vapour
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: On basis of test data.

Acute dermal toxicity : LD50 (Rabbit): > 2.5 ml/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: On basis of test data.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Skin corrosion/irritation

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Species: Rabbit
Result: No skin irritation
Remarks: On basis of test data.

Octamethylcyclotetrasiloxane:

Species: Rabbit
Result: No skin irritation
Remarks: On basis of test data.

Serious eye damage/eye irritation

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Species: Rabbit
Result: No eye irritation
Remarks: On basis of test data.

Octamethylcyclotetrasiloxane:

Species: Rabbit
Result: No eye irritation
Remarks: On basis of test data.

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Assessment: Probability or evidence of low to moderate skin sensitisation rate in humans

Test Type: Buehler Test
Species: Guinea pig
Result: positive
Remarks: On basis of test data.

Octamethylcyclotetrasiloxane:

Assessment: Does not cause skin sensitisation.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Test Type: Maximisation Test
Species: Guinea pig
Result: negative
Remarks: On basis of test data.

Germ cell mutagenicity

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: On basis of test data.

Test Type: Mutagenicity (in vitro mammalian cytogenetic test)
Result: positive
Remarks: On basis of test data.

Test Type: Chromosome aberration test in vitro
Result: positive
Remarks: On basis of test data.

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative
Remarks: On basis of test data.

Germ cell mutagenicity- Assessment : Animal testing did not show any mutagenic effects.

Octamethylcyclotetrasiloxane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: On basis of test data.

Test Type: Mutagenicity (in vitro mammalian cytogenetic test)
Result: negative
Remarks: On basis of test data.

Test Type: Chromosome aberration test in vitro
Result: negative
Remarks: On basis of test data.

Test Type: In vitro sister chromatid exchange assay in mammalian cells
Result: negative
Remarks: On basis of test data.

Test Type: DNA damage and repair, unscheduled DNA syn-

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

thesis in mammalian cells (in vitro)
Result: negative
Remarks: On basis of test data.

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: On basis of test data.

Test Type: Rodent dominant lethal test (germ cell) (in vivo)
Species: Rat
Application Route: Ingestion
Result: negative
Remarks: On basis of test data.

Germ cell mutagenicity- Assessment : Animal testing did not show any mutagenic effects.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat, male and female
Application Route: Ingestion
Symptoms: No effects on fertility
Remarks: On basis of test data.

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat, male and female
Application Route: Ingestion
Symptoms: No effects on foetal development
Remarks: On basis of test data.

Reproductive toxicity - Assessment : No evidence of adverse effects on sexual function and fertility, or on development, based on animal experiments.

Octamethylcyclotetrasiloxane:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat, male and female
Application Route: inhalation (vapour)
Symptoms: Effects on fertility
Remarks: On basis of test data.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

Effects on foetal development : Test Type: Prenatal development toxicity study (teratogenicity)
Species: Rabbit
Application Route: inhalation (vapour)
Symptoms: No effects on foetal development
Remarks: On basis of test data.

Reproductive toxicity - Assessment : Some evidence of adverse effects on sexual function and fertility, based on animal experiments.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Components:

Methyltrimethoxysilane:

Exposure routes: inhalation (vapour)

Assessment: No significant health effects observed in animals at concentrations of 1 mg/l/6h/d or less.

Exposure routes: Ingestion

Assessment: No significant health effects observed in animals at concentrations of 100 mg/kg bw or less.

Octamethylcyclotetrasiloxane:

Exposure routes: Ingestion

Assessment: No significant health effects observed in animals at concentrations of 100 mg/kg bw or less.

Exposure routes: inhalation (vapour)

Assessment: No significant health effects observed in animals at concentrations of 1 mg/l/6h/d or less.

Exposure routes: Skin contact

Assessment: No significant health effects observed in animals at concentrations of 200 mg/kg bw or less.

Repeated dose toxicity

Components:

Methyltrimethoxysilane:

Species: Rat

Application Route: inhalation (vapour)

Remarks: On basis of test data.

Species: Rat

Application Route: Ingestion

Remarks: On basis of test data.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Octamethylcyclotetrasiloxane:

Species: Rat
Application Route: Ingestion
Remarks: On basis of test data.

Species: Rat
Application Route: inhalation (vapour)
Remarks: On basis of test data.

Species: Rabbit
Application Route: Skin contact
Remarks: On basis of test data.

Aspiration toxicity

Not classified based on available information.

Further information

Components:

Octamethylcyclotetrasiloxane:

Remarks: Results from a 2 year repeated vapour inhalation exposure study to rats of octamethylcyclotetrasiloxane (D4) indicate effects (benign uterine adenomas) in the uterus of female animals. This finding occurred at the highest exposure dose (700 ppm) only. Studies to date have not demonstrated if these effects occur through pathways that are relevant to humans. Repeated exposure in rats to D4 resulted in protoporphyrin accumulation in the liver. Without knowledge of the specific mechanism leading to the protoporphyrin accumulation the relevance of this finding to humans is unknown.

SECTION 12: Ecological information

12.1 Toxicity

Components:

Methyltrimethoxysilane:

Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): > 110 mg/l
Exposure time: 96 h

Toxicity to daphnia and other : EC50 (Daphnia sp. (water flea)): > 122 mg/l
aquatic invertebrates Exposure time: 48 h

Toxicity to algae : ErC50 (Pseudokirchneriella subcapitata (green algae)): > 120
mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

Toxicity to microorganisms : EC50 : > 100 mg/l
Method: OECD Test Guideline 209

Octamethylcyclotetrasiloxane:

Toxicity to fish : LC50 (Cyprinodon variegatus (sheepshead minnow)): >

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

- 0.0063 mg/l
Exposure time: 336 h
Remarks: No toxicity at the limit of solubility
- Toxicity to daphnia and other aquatic invertebrates : EC50 (Mysidopsis bahia (opossum shrimp)): > 0.0091 mg/l
Exposure time: 96 h
Remarks: No toxicity at the limit of solubility
- Toxicity to algae : ErC50 (Pseudokirchneriella subcapitata (green algae)): > 0.022 mg/l
Exposure time: 72 h
Remarks: No toxicity at the limit of solubility
- Toxicity to fish (Chronic toxicity) : NOEC: \geq 0.0044 mg/l
Species: Oncorhynchus mykiss (rainbow trout)
Remarks: On basis of test data.
No toxicity at the limit of solubility
- Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC: \geq 0.0079 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Remarks: On basis of test data.
No toxicity at the limit of solubility

Ecotoxicology Assessment

- Chronic aquatic toxicity : May cause long lasting harmful effects to aquatic life.

12.2 Persistence and degradability

Components:

Octamethylcyclotetrasiloxane:

- Biodegradability : Result: Not readily biodegradable.
Biodegradation: 3.7 %
Exposure time: 28 d
Method: OECD Test Guideline 310
- Stability in water : Degradation half life: 69.3 - 144 h (24.6 °C)
pH: 7
Method: OECD Test Guideline 111

12.3 Bioaccumulative potential

Components:

Methyltrimethoxysilane:

- Partition coefficient: n-octanol/water : log Pow: -2.36

Octamethylcyclotetrasiloxane:

- Bioaccumulation : Species: Pimephales promelas (fathead minnow)
Bioconcentration factor (BCF): 12,400

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version 1.15 Revision Date: 07.02.2018 SDS Number: 837107-00016 Date of last issue: 22.03.2017
Date of first issue: 26.11.2014

Partition coefficient: n-octanol/water : log Pow: 6.48 (25.1 °C)

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Components:

Octamethylcyclotetrasiloxane:

Assessment : Remarks: Octamethylcyclotetrasiloxane (D4) meets the current REACH Annex XIII criteria for PBT and vPvB. In Canada, D4 has been assessed and deemed to meet the PiT criteria. However, D4 does not behave similarly to known PBT/vPvB substances. The weight of scientific evidence from field studies shows that D4 is not biomagnifying in aquatic and terrestrial food webs. D4 in air will degrade by reaction with naturally occurring hydroxyl radicals in the atmosphere. Any D4 in air that does not degrade by reaction with hydroxyl radicals is not expected to deposit from the air to water, to land, or to living organisms.

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations. According to the European Waste Catalogue, Waste Codes are not product specific, but application specific. Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

The components of this product are reported in the following inventories:

NZIoC : All ingredients listed or exempt.

AICS : All ingredients listed or exempt.

IECSC : All ingredients listed or exempt.

ENCS/ISHL : All components are listed on ENCS/ISHL or exempted from inventory listing.

PICCS : All ingredients listed or exempt.

DSL : All chemical substances in this product comply with the CEPA 1999 and NSNR and are on or exempt from listing on the Canadian Domestic Substances List (DSL).

REACH : For purchases from Dow Chemical EU legal entities, all ingredients are currently pre/registered or exempt under REACH. Please refer to section 1 for recommended uses. For pur-

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

chases from non-EU Dow Chemical legal entities with the intention to export into EEA please contact your DC representative/local office.

- TSCA : All chemical substances in this product are either listed on the TSCA Inventory or are in compliance with a TSCA Inventory exemption.
- KECI : All ingredients listed, exempt or notified.
- TCSI : All ingredients listed or exempt.

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

Full text of H-Statements

- H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H317 : May cause an allergic skin reaction.
H361f : Suspected of damaging fertility.
H413 : May cause long lasting harmful effects to aquatic life.

Full text of other abbreviations

- Aquatic Chronic : Chronic aquatic toxicity
Flam. Liq. : Flammable liquids
Repr. : Reproductive toxicity
Skin Sens. : Skin sensitisation
DCC OEL : Dow Chemical Guide
GB EH40 : UK. EH40 WEL - Workplace Exposure Limits
US WEEL : USA. Workplace Environmental Exposure Levels (WEEL)
DCC OEL / TWA : Time weighted average
GB EH40 / TWA : Long-term exposure limit (8-hour TWA reference period)
US WEEL / TWA : Time weighted average

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisa-

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DOWSIL™ 744 RTV Sealant White

Version	Revision Date:	SDS Number:	Date of last issue: 22.03.2017
1.15	07.02.2018	837107-00016	Date of first issue: 26.11.2014

tion for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

GB / EN