



Residual current circuit breaker (RCCB), 40A, 4p, 300mA, type G/F

Part no. PFIM-40/4/03-G/F
Article no. 187360



Similar to illustration

Delivery programme

Basic function			Residual current circuit breakers
Number of poles			4 pole
Application			Switchgear for residential and commercial applications
Rated current	I_n	A	40
Rated short-circuit strength	I_{cn}	kA	10 with back-up fuse
Rated fault current	$I_{\Delta N}$	A	0.3
Type			Typ G/F (ÖVE E 8601)
Tripping		A	Short time-delayed
Product range			PFIM-F
Sensitivity			pulse-current sensitive - frequency composition (10 Hz, 50 Hz, 1000 Hz)
Impulse withstand current			surge-proof 5 kA

Technical data

Electrical

Types conform to			IEC/EN 62423
Current test marks			As per inscription
Rated operating voltage	U_n	V AC	230/400
Rated frequency	f	Hz	50
Limit values of the operating voltage			
Test circuit		V AC	196 - 456
Rated frequency	f	Hz	50
Sensitivity			pulse-current sensitive - frequency composition (10 Hz, 50 Hz, 1000 Hz)
Rated insulation voltage	U_i	V	440
Rated impulse withstand voltage	U_{imp}	kV	4 (1.2/50 μ s)
Rated short-circuit strength	I_{cn}	kA	10 with back-up fuse
Max. admissible back-up fuse			
Short-circuit	gG/gL	A	63
Overload	gG/gL	A	25
Rated making and breaking capacity / Rated residual making and breaking capacity	$I_m / I_{\Delta m}$	A	500
lifespan			
Electrical		Operations	 2000
Mechanical		Operations	 10000

Mechanical

Standard front dimension		mm	45
Device height		mm	80
Built-in width		mm	70 (4TE)
Mounting			Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
Degree of Protection			IP20 switches IP 40 enclosed
Terminals top and bottom			Twin-purpose terminals
Terminal protection			Busbar tag shroud to BGV A3, ÖVE-EN 6
Terminal cross-section			
Solid		mm ²	1.5 - 35
Stranded		mm ²	2 x 16
Terminal cross-section			M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, Pozidriv PZ2)

Tightening torque of fixing screws		N/m	2 - 2.4
Thickness of busbar material		mm	0.8 - 2
Admissible ambient temperature range		°C	-25 - +40
Permissible storage and transport temperatures		°C	-35 - +60
Climatic proofing			according to IEC/EN 61008
Mounting position			As required
Contact position indicator			red / green

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I_n	A	40
Equipment heat dissipation, current-dependent	P_{vid}	W	13.1
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			
			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			
			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			
			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			
			Meets the product standard's requirements.
10.2.5 Lifting			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			
			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			
			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			
			Meets the product standard's requirements.
10.5 Protection against electric shock			
			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			
			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			
			Is the panel builder's responsibility.
10.8 Connections for external conductors			
			Is the panel builder's responsibility.
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			
			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			
			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			
			Is the panel builder's responsibility.
10.10 Temperature rise			
			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			
			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			
			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			
			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 6.0

Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)			
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss8.1-27-14-22-01 [AAB906011])			
Number of poles			4
Nominal rated voltage		V	230
Nominal rated current		A	40
Rated fault current		A	0.3
Mounting method			DIN rail
Leakage current type			-
Selective protection			No
Short-circuit breaking capacity (I _{cw})		kA	10
Surge current capacity		kA	3
Frequency			50 Hz
Additional equipment possible			Yes

Degree of protection (IP)			IP20
Construction size (in accordance with DIN 43880)			1
Width in number of modular spacings			4
Built-in depth		mm	70.5
Short-time delayed tripping			Yes