

## SPE PCB connector - SPE-T1-STRM-90 - 1163797

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




SPE PCB connector, type: IEC 63171-2, degree of protection: IP20, number of positions: 2, CAT B (ISO/IEC 63171), connection method: THR solder connection, Single Pair Ethernet

### Your advantages

- ✓ Compact design for maximum space savings
- ✓ Connectors in accordance with IEC 63171-2
- ✓ Robust industrial design
- ✓ 360° shielding
- ✓ THR solderable
- ✓ Data transmission up to 600 MHz



### Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 063151 175979
GTIN	4063151175979
Weight per Piece (excluding packing)	3.960 g
Sales Key	ABNABB

### Technical data

#### Dimensions

Width	5 mm
Height	8.35 mm
Length	14.2 mm

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP20

# SPE PCB connector - SPE-T1-STRM-90 - 1163797

## Technical data

### General

Number of positions	2
Insulation resistance	> 1 TΩ
Overvoltage category	I
Degree of pollution	2
Connection method	THR solder connection
Insertion/withdrawal cycles	≥ 750
Transmission characteristics (category)	CAT B (ISO/IEC 63171)
Halogen-free	yes
Resistance to oil	yes
Flame resistance	UL 94 V0
Locking type	Locking clip
Rated voltage (III/2)	72 V DC
Rated current	4 A

### Material

Flammability rating according to UL 94	V0
Contact material	Cu alloy
Contact surface material	Ni/Au
Contact carrier material	LCP

### Cable

Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250 V DC
Flame resistance	UL 94 V0
Halogen-free	yes
Resistance to oil	yes

### Connection data for connection 1

Rated current	4 A
Rated voltage (III/2)	72 V DC
Specification	IEC 60068-2-58
	IPC-A-610
	IPC/JEDEC J-STD-020
Moisture Sensitive Level	MSL1

### Standards and Regulations

Flame resistance	UL 94 V0
Resistance to oil	yes
Halogen-free	yes
Flammability rating according to UL 94	V0
Standards/regulations	IEC 63171
	IEC 63171-2
	IEEE 802.3bu

# SPE PCB connector - SPE-T1-STRM-90 - 1163797

## Technical data

### Standards and Regulations

	IEEE 802.3cg
	IEEE 802.3bw
	IEEE 802.3bp

## Classifications

### eCl@ss

eCl@ss 10.0.1	27440390
eCl@ss 11.0	27440390
eCl@ss 9.0	27440402

## Accessories

### Accessories

#### Data cable preassembled

Patch cable - SPE-T1-CCP-SF/1,0/AWG22/CCP-SF - 1183807



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 1 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Patch cable - SPE-T1-CCP-SF/2,0/AWG22/CCP-SF - 1183808



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 2 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

Patch cable - SPE-T1-CCP-SF/3,0/AWG22/CCP-SF - 1183810



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 3 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet

## SPE PCB connector - SPE-T1-STRM-90 - 1163797

### Accessories

Patch cable - SPE-T1-CCP-SF/5,0/AWG22/CCP-SF - 1183811



Patch cable, type: IEC 63171-2, degree of protection: IP20, cable length: 5 m, number of positions: 2, 1 Gbps, connection method: Crimp connection, connection cross section: AWG 22- 22, Single Pair Ethernet