

Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):4,5 /18,5; UPRI(V):550-525-500-480-  
 460- 440-415-400-380-230-208; USEC(V):2X115;  
 ISEC(A):2X19,6; F(HZ):50...60; VECTOR GR./SHIELD  
 WNG.:II0 /0; TA/ISOKL:55 /H; IP23; TYPE OF  
 TERMINALS:SCREW CONNECTION;  
 INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4  
 >CONTROL CIRCUIT TRANSFORMER< >ISOLATION  
 TRANSFORMER<

General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	4 500
Efficiency		0.94
Connection method for transformers		II0
Certificate of suitability		CE
Product function		
• Temperature monitoring		No
• Insulation monitoring		No
• Short-circuit and overload proof		No
Number of shielding windings		0
Short-term vector power	V·A	19 000
Relative short-circuit voltage	%	3.9

Inputs:

Phase number of the inputs		1
Input voltage		
• _1 Rated value	V	550
• _2 Rated value	V	525
• _3 Rated value	V	500
• _4 Rated value	V	480
• _5 Rated value	V	460
• _6 Rated value	V	440
• _7 Rated value	V	415

• _8 Rated value	V	400
• _9 Rated value	V	380
• _10 Rated value	V	230
• _11 Rated value	V	208
<b>Electrical input frequency</b>		
• minimum	Hz	50
• maximum	Hz	60

#### Outputs:

<b>Phase number of the outputs</b>		1
<b>Output voltage</b>		
• _1 Rated value	V	230
• _2 Rated value	V	115
<b>Electrical output frequency</b>		
• maximum	Hz	60
• minimum	Hz	50




#### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		H
<b>Ambient temperature Rated value</b>	°C	55
<b>Protection class IP</b>		IP23

#### Mechanical data:

<b>Type of electrical connection</b>		
• at output for main current circuit		screw-type terminals
• at input for main current circuit		screw-type terminals
<b>Mounting type</b>		screws
<b>Construction form of the iron core</b>		UI 180/75
<b>Width</b>	m	0.351
<b>Height</b>	m	0.395
<b>Depth</b>	m	0.33

#### Certificates/ approvals:

<b>General Product Approval</b>	<b>Shipping Approval</b>	<b>other</b>
		
		<a href="#">other</a> <a href="#">Declaration of Conformity</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**  
<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**  
<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AT36128DD400FC0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AT36128DD400FC0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AT36128DD400FC0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AT36128DD400FC0&lang=en)

**last modified:**

15.01.2015