

Die, HSSE G right, nitrided, pre-slotted and 2.0 thread chamfer

for universal use up to 1300 N/mm²

ATORN[®]

Application

For cutting G (pipe) threads externally in the material groups of steel, stainless steel, non-ferrous metals and special alloys up to a strength of 1300 N/mm².

Version

- right die. tol. A with spiral point, nitrided, pre-slotted and 2.0 pitch

Advantage

- specialised application with optimised cutting geometry for use in difficult-to-machine materials
- micro cut edge treatment and special lapping method for excellent process reliability and long service life



| Application | Steel (N/mm ²) | | | Stainless steel | | Alu | | Brass | | Bronze | | Plas-tics | Graphite G(C)FK | GG(G) GjMW | Titan-alloy | Nickel-alloy | Super-alloy | Hard mat. | |
|-------------|----------------------------|-------|-------|-----------------|---------|-------|------|-------|------|--------|------|-----------|-----------------|------------|-------------|--------------|-------------|-----------|---------|
| | <700 | <1000 | <1300 | marten. | austen. | short | long | short | long | short | long | | | | | | | <55 HRC | <65 HRC |
| | | ● | ● | ● | ● | ● | | | | | ● | | | | ● | ● | ● | | |

| | |
|---|--------------------|
| Art. No. | 13484 040 |
| Thread type | Pipe thread |
| Cutting material | HSSE |
| Tolerance of dies | A |
| Thread type x nominal diameter in inches | G 1/2 in |
| Number of thread starts per inch | 14 |
| Outer diameter | 45 mm |
| Height | 14 mm |
| Cutting direction | Right-hand cutting |

EAN-Code

4050293116205