

Shrink-fit chuck, 3 degrees

Long, slim design

ATORN[®]

Application

For clamping cutters and drills with straight shanks in h6 tolerance. Suitable for heavy-duty machining and all high-power applications. Suitable for inductive, contact and hot air shrinking devices.



Version

- guaranteed maximum concentricity 0.003 mm
- shrink grip and shrink release of HM and HSS tools
- hardness 52 + 2 HRC
- maximum coolant pressure 80 bar
- Glass bead blasted

Advantage

- Slimline design, extremely low interference contour
- High transmittable torques
- High positioning and repeat accuracy
- Ideal for high rotation speeds

Art. no.	23427 359
Clamping diameter	12 mm
Tapered diameter	18 mm
Outer diameter	27 mm
Projecting length	120 mm
Max. clamp in depth	47 mm
Suitable for thread	M10 x 1
Width across flats	5 mm
Max. adjustment travel	10 mm
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293440348