


NOTES:

SPECIFIC LENGTHS.

T	1	
SPECIFICATIONS		
CONTACT CARRIER MATERIAL	NYLON or TPU	
CONTACT MATERIAL/PLATING	BRASS/GOLD	
HOUSING, LOCKNUT MATERIAL/PLATING	BRASS/NICKEL	
O-RING MATERIAL	NITRILE	
RATED CURRENT [A]	4.0 A	
RATED VOLTAGE [V]	250 V	
CONDUCTOR INSULATION MATERIAL	PVC	
NUMBER OF CONDUCTORS [AWG]	4x22 AWG	
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)	
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68	



CABLE LENGTH	TOLERANCE	
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER	
STRIP LENGTH	TOLERANCE	
0-7mm	±0.5mm	
8-29mm	±1.0mm	
30-49mm	±2.0mm	
50-69mm	±3.0mm	
70-100mm	±4.0mm	
OVER 100mm	±5.0mm	

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS	3RD ANGLE PROJECTION	THIS DRAWING IS
1. 2. 3. 4.	⊕ ←	TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.
MATERIAL		DRFT JBJ
SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DSGN
		UNIT OF MI
FINISH	1	

turck inc High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com

REV

DATE 02/08/01 JBJ FK 4.4-* SCALE

1 = .8UNIT OF MEASUREMENT IDENTIFICATION NO.

UPDATE DRAWING SPECIFICATION, ADD END VIEW, SEE ECO RWC 01/03/1 33860 DESCRIPTION DATE ECO NO.

1. "*" INDICATES LEAD LENGTH IN METERS. CONTACT TURCK TO ORDER

SEE SPECIFICATIONS

CONTACT TURCK FOR MORE INFORMATION

MILLIMETER [INCH]

DO NOT SCALE THIS DRAWING FILE: 777000190 SHEET 1 OF 1