


**DB M 1 150 (961 110)**


- Coordinated spark-gap-based lightning current arrester consisting of a base part and a plug-in protection module
- Maximum system availability due to RADAX Flow follow current limitation
- Directly coordinated with DEHNguard surge protective devices without additional cable length



Figure without obligation



Basic circuit diagram DB M 1 150



Dimension drawing DB M 1 150

Coordinated and modular single-pole lightning current arrester with high follow current limitation.

Type Part No.	DB M 1 150 961 110
SPD according to EN 61643-11 / IEC 61643-11	type 1 / class I
Nominal voltage (a.c.) ( $U_N$ )	120 V (50 / 60 Hz)
Max. continuous operating voltage (a.c.) ( $U_C$ )	150 V (50 / 60 Hz)
Lightning impulse current (10/350 $\mu$ s) ( $I_{imp}$ )	35 kA
Specific energy (W/R)	306.25 kJ/ohms
Voltage protection level ( $U_P$ )	$\leq 1.5$ kV
Follow current extinguishing capability (a.c.) ( $I_n$ )	35 kA <sub>rms</sub>
Follow current limitation / Selectivity	no tripping of a 32 A gG fuse up to 35 kA <sub>rms</sub> (prosp.)
Response time ( $t_A$ )	$\leq 100$ ns
Max. backup fuse (L) up to $I_k = 35$ kA <sub>rms</sub> ( $t_a \leq 0.2$ s)	500 A gG
Max. backup fuse (L) up to $I_k = 35$ kA <sub>rms</sub> ( $t_a \leq 5$ s)	315 A gG
Max. backup fuse (L) for $I_k > 35$ kA <sub>rms</sub>	200 A gG
Max. backup fuse (L-L')	125 A gG
Temporary overvoltage (TOV) ( $U_T$ ) – Characteristic	230 V / 120 min. – withstand
Operating temperature range (parallel connection) ( $T_{UP}$ )	-40 °C ... +80 °C
Operating temperature range (series connection) ( $T_{US}$ )	-40 °C ... +60 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (L/N, L'/N', N/PE (N)) (min.)	10 mm <sup>2</sup> solid / flexible
Cross-sectional area (L/N, N/PE(N)) (max.)	50 mm <sup>2</sup> stranded / 35 mm <sup>2</sup> flexible
Cross-sectional area (L'/N') (max.)	35 mm <sup>2</sup> stranded / 25 mm <sup>2</sup> flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
Approvals	UL, CSA
Weight	317 g
Customs tariff number	85363090
GTIN	4013364118560
PU	1 Stk

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.