

Angular milling cutter HSSE Co 5




Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Version:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery and end face



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	34	27	20	18	15	70	175	70	70	45	45	60		30					

Art. no.	15814 120
Cutting material	HSSE Co5
Type	N
Number of cutting edges	10 PCS
Chamfer angle	60 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	16 mm
Width of cutting edge	6.3 mm
Immersion depth	15 mm
Length	60 mm
Shaft diameter	12 mm
Form	C
fz steel 700	0.04 mm

EAN-Code

4039247098118