

## Miniature cutting insert, type AG HW56 15

For internal recessing

**ATORN**<sup>®</sup>



### Application

For internal recessing in the material groups steel and (stainless steel) at low to high cutting speeds and under average cutting conditions.

### Version

- Solid carbide cutting insert with internal cooling

### Advantage

- Very hard cemented carbide grade ensures low wear
- Stable geometry for the cutting insert
- Extremely sharp blades ensure process reliability for cutting

<b>Art. no.</b>	<b>17129 642</b>
<b>ISO name</b>	AG
<b>Shaft diameter</b>	5 mm
<b>Length</b>	51 mm
<b>Clearance length</b>	22 mm
<b>Programming size 2</b>	1.2 mm
<b>Recessing width</b>	2 mm
<b>Programming size</b>	2.3 mm
<b>Min. bore diameter</b>	5.1 mm
<b>Machining direction</b>	Left
<b>Carbide type</b>	HW56 15
<b>Material to be processed</b>	Stainless steel, Non-ferrous metal

### EAN-Code

4050293378382