

## Manual chain hoist

Made of aluminium

### Application:

For the ergonomic lifting of heavy materials and products.

### Execution:

- Almost completely closed aluminium housing
- Galvanised load chain in line with DIN EN 8 18-7 (quality class T)
- Galvanised manual chain in line with DIN 766
- 360° rotating safety hook
- Ball bearing mounted precision gears
- Threaded automatic mechanical brake

### Advantage:

- High resistance to corrosion
- High lifting speed



<b>Art. no.</b>	<b>77165 066</b>
<b>Load-carrying capacity</b>	1000 kg
<b>Nominal chain thickness</b>	19.1 mm
<b>Chain diameter</b>	6.3 mm
<b>Stroke force at nominal load</b>	35 daN
<b>Lift height every 1 m hand chain is uncoiled</b>	29 mm
<b>Lift height</b>	3000 mm
<b>Min. hook spacing</b>	365 mm
<b>Number of load chains</b>	1 PCS
<b>Gross Weight</b>	11.600 kg
<b>Product Group</b>	7EH

### EAN

4036475702022