



### H-1/2D3500 Specifications



<b>Nominal Capacity</b>	<b>3500mAh</b>
<b>Nominal Voltage</b>	<b>1.2V</b>
<b>Internal Impedance (at 1000Hz)</b>	<b>&lt;20m<math>\Omega</math></b>
<b>Charge</b>	
<b>Standard Charge</b>	<b>350mA x 16h</b>
<b>Fast Charge</b>	<b>3500mA x 1.2h</b>
<b>Discharge Cut-off Voltage</b>	<b>1.0V</b>
<b>Max Dimension (with tube)</b>	
<b>Diameter</b>	<b>32.5mm</b>
<b>Height</b>	<b>33.5mm</b>
<b>Weight</b>	<b>85 g</b>
<b>Operating Temperature</b>	
<b>Standard charge</b>	<b>0 ~ 40°C</b>
<b>Fast charge</b>	<b>10 ~ 35°C</b>
<b>Trickle charge</b>	<b>0 ~ 45°C</b>
<b>Discharge</b>	<b>-10 ~ 50°C</b>
<b>Storage Temperature</b>	
<b>More than 1 month</b>	<b>0 ~ 40°C</b>
<b>More than 3 months</b>	<b>0 ~ 30°C</b>
<b>More than 12 months</b>	<b>0 ~ 25°C</b>

Charge at 20°C



Discharge at high rate, 20°C

