



MS3V-T1R

Tuning Fork Crystal 30 kHz – 200 kHz



DIMENSIONS



All dimensions in mm typical

Miniature SMT package
Package height 1.48 mm max.
Compatible solder pad layout with plastic molded crystal packages
Industrial temperature range
Very price competitive
Low aging
Low power consumption
High shock and vibration resistance

DESCRIPTION:

The MS3V-T1R is a miniature square-bodied 1.4 x 6.7 x 1.4 mm metal package with formed leads, intended for surface mounting and reflow soldering.

Within the package is a high-quality tuning fork quartz crystal resonator, manufactured with a precision high-volume photolithographic process and operating in the fundamental mode.

Due to highly automated, large-volume production, the MS3V-T1R is very price competitive and ideal for any consumer and industrial applications.

For pick-and-place equipment, the crystals are supplied in 16 mm tape:

7" (178 mm) reel with 2'000 crystals

13" (330 mm) reel with 9'000 crystals

ELECTRICAL CHARACTERISTICS AT 25°C:

Frequency Range	F_L	30–200	kHz
Load capacitance ¹⁾	C_L	7.0 / 9.0 / 12.5	pF
Frequency tolerance ²⁾	$\Delta F/F$	+/-20	ppm
	$\Delta F/F$	+/-100	ppm
Drive level max.	P	1.0	μW
Insulation resistance min.	R_i	500	M Ω
Aging first year max.	$\Delta F/F$	+/-3	ppm

Frequency Example ³⁾	F_L	32.768	75.000	76.800	kHz
Series resistance typ./max.	R_s	50 / 65	19 / 30	18 / 30	k Ω
Motional capacitance typ.	C_1	2.1	1.45	1.35	fF
Static capacitance typ.	C_0	0.9	0.9	0.9	pF
Turnover temperature	T_0	25 +/-5	22 +/-5	22 +/-5	$^{\circ}C$
Frequency vs. temperature	$\Delta F/F_0$	$-0.035 \text{ ppm}/^{\circ}C^2 (T - T_0)^2$ +/-10%			ppm

1) For standard and other load capacitances consult factory.

2) Tighter and wider frequency tolerances on request.

3) Values for other frequencies consult factory.

STANDARD FREQUENCIES:

Frequency kHz				
32.768	38.400	75.000	76.800	77.500
Other frequencies on request				

ENVIRONMENTAL CHARACTERISTICS:

		Conditions	Max. Dev.
Storage temperature range		-55 to +85°C	
TA Operating temperature range		-40 to +85°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, 1/2 sine	+/-5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	+/-5 ppm

TERMINATIONS AND PROCESSING:

Type	Termination	Processing
MS3V-T1R	Can: Au flashed Leads: Formed leads Au flashed	For SMD mounting Reflow soldering 260°C / 20 sec. max

PRODUCT DESCRIPTION AND ORDERING INFORMATION:

MS3V-T1R 32.768kHz 12.5pF +/-20ppm TA QC

Frequency F₀
C_L Load Capacitance
 7.0 pF
 9.0 pF
 12.5 pF
Frequency tolerance
 +/- 20 ppm
 +/- 100 ppm

Temperature Range
 TA = -40 to 85°C (Standard)

Optional:
 if not defined,
 'Standard' will apply

Qualification
 QC = Commercial (Standard)

A unique part number will be generated for each product specification, i.e:
 20xxxx-ML02 2'000 pcs (in 16mm tape on 7" reel)
 20xxxx-PL09 9'000 pcs (in 16mm tape on 13" reel)
 Please contact us.

All specifications subject to change without notice.



Micro Crystal AG
 Mühlestrasse 14
 CH-2540 Grenchen
 Switzerland

Tel. +41 32 655 82 82
 Fax +41 32 655 82 83
 sales@microcrystal.com
 www.microcrystal.com