
Inductor






RoHS Compliant


Note:

1. Wire UEFN/U (155°C) Ø0.5mm

2. 76TS (Reference) C.W

Configurations and Dimensions





А	23mm (Max.)
В	12.5mm (Max.)
С	12 ±1mm
D	1mm (Min.)
F	Ø0.5mm (Ref.)

Test Data for Mechanical

Test Item	A mm	B mm	C mm	D mm	F mm	
Specification	23 (Max.)	12.5 (Max.)	12 ±1	1 (Min.)	Ø0.5 (Ref.)	
1	22	11.54	11.58	1.82	0.51	
2	22.37	11.46	12.69	1.85	0.5	
3	21.99	11.71	11.96	1.89	0.51	
4	22.15	11.27	12.15	1.9	0.51	
5	22.26	11.46	11.92	1.84	0.52	
Average	22.15	11.49	12.06	1.86	0.51	

Material List

No.	ltem	Material Description
1	Core	T80B-75-TAF200 (Red / White)
2	Wire	Ø0.5mm UEFN/U (155°C)
3	Solder (Lead-free)	Sn99.3% / Cu0.7%

Electrical Characteristics

Test Condition		
10kHz / 5mA	L	390µH ±15%
TA = 25°C	DCR	250mΩ (Max.)
10kHz / 5mA Irms = 1A	ΔT	Temperature rise 40°C (Max.)

Operating temperature : -55°C to +130°C

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Reliability Test

Test Item	Specifications		Test M	Test Method and Remarks	
Operating temperature range	-55°C to +130°C		Including temperature	rise due to self-generated heat.	
Storage condition	Ambient temperature: 0°C to 40°CHumidity: Below 70% RH		To maintain the solderability of terminal electrodes, care must be taken to control temperature and humidity in the storage area.		
Moisture sensitivity	Appearance DCR change Inductance change	: No abnormality No damage : Within ±5% : Within ±5%	According to J-STD-02 Test condition Test duration Recovery	 0B level 3 : 60°C 60% RH : 40 hrs : 1 to 2 hours of recovery under the standard condition after the removal from the test chamber. 	
Solderability	All termination shall exhibit a continuous solder coating free from defects for a minimum of 95% of the surface area of any individual lead.		According to J-STD-00 Steam aging category Steam aging duration Solder Solder temperature Dip time	: 97°C 98% RH	

Test Data for Electrical

Test Item	L µH	DCR mΩ	ΔΤ
Condition	10kHz / 5mA	TA = 25°C	10kHz / 5mA Irms = 1A
Specification	390 ±15%	250 (Max.)	Temperature rise 40°C (Max.)
1	389.24	207.6	
2	390.03	198.9	
3	393.78	214.2	ОК
4	389.42	212.8	
5	396.89	220.4	
Average	391.87	210.78	ОК

Part Number Table

Description	Part Number
Inductor, 390µH, 15%, 2 Pins	MCAP108224076A-391LU

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

