**Coaxial Cable** 



# multicomp PRO

# RoHS Compliant

### Product Description:

	PP000616	PP000617	PP000618	PP000619
Application	For communication and signal control systems			
Multi-construction	1			
Coaxial Cable Type	URM76	URM203	URM76	URM70

#### **Construction:**

Single	Bare Copper			
Construction	0.3 ±0.008 × 7	1.12 ±0.02	0.3 ±0.008 × 7	0.19 ±0.008 × 7
Stranded Dia.(mm)	0.92	1.12	0.92	0.58
Insulation	Solid PE	Gas injection Foam PE	Solid PE	Solid PE
Thickness	1.01	2.01	1.01	1.25
Insulation Dia.	2.95 ±0.15mm	5.15 ±0.2mm	2.95 ±0.15mm	3.2 ±0.15mm
Insulation Colour	Natural			
Braiding	Bare Copper			
Construction (stranded)	0.12 ±0.008 × 16 × 6	0.12 ±0.008 × 16 × 6	0.12 ±0.008 × 16 × 6	0.12 ±0.008 × 16 × 6
Braiding coverage	85%	65%	85%	81%
Jacket	LSZH	PVC	PVC	PVC
Thickness (mm)	0.75	0.9	0.75	0.85
Dia.(±0.2mm)	5	7.3	5	5.8
Jacket Colour	Black			
Packaging	100m Reel	100m Drum	100m Reel	100m Cardboard Reel

# **Electrical Characteristics:**


Description	Part Number			
Description	PP000616	PP000617	PP000618	PP000619
DC Resistance inner core .at 20°C (Ω/km)	<38.3	<19.2	<38.3	<95.5
Min. Insulation DC Resistance at 20°C (M $\Omega$ ×km)	500	500	500	>500
Operating Temperature Range	-40°C to +70°C			
Rated Voltage(V)	2kV RMS	2.4kVrмs	4kVrms	1.8kVrмs
Capacitance(pF/m)	100 ±5	52±4	100 ±5	<70
Velocity ratio (%)	66.7	82	66.7	66.7%
Impedance(Ω)	50 ±3	75 ±3	50 ±3	75 ±3

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Description	Part Number			
Description	PP000616	PP000617	PP000618	PP000619
Attenuation at 20°C (-dB/100m) (±10%)			Ì	
5 MHz	5.9	-	5.9	-
50 MHz	10.3	-	10.3	-
100 MHz	14.8	-	14.8	15
230 MHz	23	-	23	-
300 MHz	27	-	27	-
470 MHz	34.2	-	34.2	-
800 MHz	47	-	47	-
860 MHz	49	-	49	-
1,000 MHz	53	-	53	52

# Design:



Description	Part Number
Cable, Coaxial, 100m, Black, URM76, LSZH	PP000616
Cable, Coaxial, 100m, Black, URM203	PP000617
Cable, Coaxial, 100m, Black, URM76, PVC	PP000618
Cable, Coaxial, 100m, Black, URM70	PP000619

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet sheet sheet sheet sheet sheet he Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

