

## DMVB/CAMV

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

PRODUCT NAME: 24669 DRAPER MED VISCOSITY SUPERGLUE DMVB-CAMV

APPLICATIONS: ADHESIVE

SUPPLIER: Draper Tools Ltd  
Hursley Road  
Chandlers Ford  
Eastleigh  
Hampshire  
SO53 1YF  
Draper Helpline +44 (0) 2380 494344

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification

###### Physical hazards

Not Classified

###### Health hazards

Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 STOT SE 3 - H335

###### Environmental hazards

Not Classified

#### 2.2. Label elements

##### Pictogram



##### Signal word

Warning

##### Hazard statements

H315 Causes skin irritation.  
H319 Causes serious eye irritation.  
H335 May cause respiratory irritation.

##### Precautionary statements

**DMVB/CAMV**

- P261 Avoid breathing vapour/spray.
- P264 Wash contaminated skin thoroughly after handling.
- P271 Use only outdoors or in a well-ventilated area.
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P302+P352 IF ON SKIN: Wash with plenty of water.
- P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P312 Call a POISON CENTER/doctor if you feel unwell.
- P321 Specific treatment (see medical advice on this label).
- P332+P313 If skin irritation occurs: Get medical advice/attention.
- P337+P313 If eye irritation persists: Get medical advice/attention.
- P362+P364 Take off contaminated clothing and wash it before reuse.
- P403+P233 Store in a well-ventilated place. Keep container tightly closed.
- P405 Store locked up.
- P501 Dispose of contents/container in accordance with national regulations.

**Supplemental label information**

EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Contains ethyl 2-cyanoacrylate

**2.3. Other hazards**

**SECTION 3: Composition/information on ingredients**

**3.2. Mixtures**

ethyl 2-cyanoacrylate	60-100%
CAS number: 7085-85-0 EC number: 230-391-5	
<b>Classification</b>	<b>Classification (67/548/EEC or 1999/45/EC)</b>
Skin Irrit. 2 - H315	
Eye Irrit. 2 - H319	
STOT SE 3 - H335	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

**SECTION 4: First aid measures**

**4.1. Description of first aid measures**

**General information**

Get medical advice/attention if you feel unwell.

**Inhalation**

Move affected person to fresh air at once. Get medical attention if any discomfort continues.

**Ingestion**

Ensure that breathing passages are not obstructed. The product will polymerise immediately in the mouth making it almost impossible to swallow. Saliva will slowly separate the solidified product from the mouth (several hours).

**Skin contact**

If adhesive bonding occurs, do not force skin apart. It may be gently peeled apart using a blunt object such as a spoon, preferably after soaking in warm soapy water. Cyanoacrylates give off heat on solidification. In rare cases a large a large drop will generate enough heat to cause a burn. Burns should be treated normally after the adhesive has been removed from the skin if lips are accidentally stuck together apply warm water to the lips and encourage maximum wetting and pressure from saliva inside the mouth. Peel or roll lips apart. Do not try to pull apart with direct opposing action.

**Eye contact**

If the eye is bonded closed, release eyelashes with warm water by covering with wet pad. cyanoacrylate will bond to eye protein and will cause periods of weeping which will help to de-bond the adhesive. Keep eye covered until de-bonding is complete,

## DMVB/CAMV

usually within in 1-3 days. Medical advice should be sought in case solid particles of cyanoacrylate trapped behind the eyelid cause any abrasive damage.

### **4.2. Most important symptoms and effects, both acute and delayed**

#### **General information**

Treat symptomatically.

### **4.3. Indication of any immediate medical attention and special treatment needed**

#### **Notes for the doctor**

Apply a pad soaked in warm water and allow the eyelids to separate. If adhesive bonding occurs, prise the skin apart slowly, working from the edge of the bonded area. Treat symptomatically.

---

## **SECTION 5: Firefighting measures**

### **5.1. Extinguishing media**

#### **Suitable extinguishing media**

Extinguish with foam, carbon dioxide or dry powder.

### **5.2. Special hazards arising from the substance or mixture**

#### **Specific hazards**

The product is not flammable. Trace amounts of toxic fumes may be released on incineration and the use of breathing apparatus is recommended.

### **5.3. Advice for firefighters**

#### **Protective actions during firefighting**

Trace amounts of toxic fumes may be released on incineration and the use of breathing apparatus is recommended.

---

## **SECTION 6: Accidental release measures**

### **6.1. Personal precautions, protective equipment and emergency procedures**

#### **Personal precautions**

Avoid contact with skin and eyes. Provide adequate ventilation.

### **6.2. Environmental precautions**

#### **Environmental precautions**

The product is biodegradable.

### **6.3. Methods and material for containment and cleaning up**

#### **Methods for cleaning up**

Provide adequate ventilation. Do not use cloths for mopping up. Polymerise with water and scrape off floor.

### **6.4. Reference to other sections**

#### **Reference to other sections**

For waste disposal, see Section 13. For personal protection, see Section 8.

---

## **SECTION 7: Handling and storage**

### **7.1. Precautions for safe handling**

#### **Usage precautions**

For personal protection, see Section 8.

### **7.2. Conditions for safe storage, including any incompatibilities**

#### **Storage precautions**

Store at temperatures between 2°C and 8°C.

### **7.3. Specific end use(s)**

#### **Specific end use(s)**

The identified uses for this product are detailed in Section 1.2.

---

## **SECTION 8: Exposure Controls/personal protection**

DMVB/CAMV

**8.1. Control parameters**

**Occupational exposure limits**

**ethyl 2-cyanoacrylate**

Short-term exposure limit (15-minute): WEL 0.3 ppm 1.5 mg/m<sup>3</sup>

WEL = Workplace Exposure Limit

**8.2. Exposure controls**

**Protective equipment**



**Eye/face protection**

Wear eye protection.

**Hand protection**

Wear protective gloves made of the following material: Polyethylene. polypropylene Do NOT use Polyvinyl chloride (PVC). Rubber (natural, latex). nylon cotton

---

**SECTION 9: Physical and Chemical Properties**

---

**9.1. Information on basic physical and chemical properties**

**Appearance**

Liquid.

**Colour**

Clear.

**Odour**

Characteristic.

**Odour threshold**

No information available.

**pH**

Not applicable.

**Melting point**

No information available.

**Initial boiling point and range**

150°C @

**Flash point**

85°C

**Evaporation rate**

Not available.

**Flammability (solid, gas)**

Not applicable.

**Upper/lower flammability or explosive limits**

No information available.

**Vapour pressure**

.293 mm Hg @ °C

**Vapour density**

No information available.

**Relative density**

No information available.

**Solubility(ies)**

## DMVB/CAMV

Insoluble in water. Soluble in the following materials: Acetone.

### **Partition coefficient**

No information available.

### **Auto-ignition temperature**

No information available.

### **Decomposition Temperature**

No information available.

### **Explosive properties**

No information available.

## **9.2. Other information**

### **Other information**

None.

---

## **SECTION 10: Stability and reactivity**

### **10.1. Reactivity**

Polymerisation will occur in the presence of moisture and other basic materials.

### **10.2. Chemical stability**

#### **Stability**

Stable at normal ambient temperatures and when used as recommended.

### **10.3. Possibility of hazardous reactions**

Polymerisation will occur in the presence of moisture and other basic materials.

### **10.4. Conditions to avoid**

None known.

### **10.5. Incompatible materials**

#### **Materials to avoid**

Moisture.

### **10.6. Hazardous decomposition products**

---

## **SECTION 11: Toxicological information**

### **11.1. Information on toxicological effects**

#### **Toxicological effects**

Considered low toxicity.

#### **Inhalation**

Vapours may irritate eyes and respiratory system May cause inhalation hypersensitivity (occupational asthma) in sensitive individuals.

#### **Ingestion**

Cyanoacrylates are considered to have relatively low toxicity. It is almost impossible to swallow as it rapidly polymerises in the mouth.

#### **Skin contact**

Bonds skin and eyes in seconds. May cause skin irritation.

#### **Eye contact**

Bonds skin and eyes in seconds. In a dry atmosphere vapours may cause irritation and lachrymatory effect.

---

## **SECTION 12: Ecological information**

### **Ecotoxicity**

There are no data on the ecotoxicity of this product.

### **12.1. Toxicity**

## DMVB/CAMV

Low

### **12.2. Persistence and degradability**

#### **Persistence and degradability**

The product is biodegradable.

### **12.3. Bioaccumulative potential**

No data available on bioaccumulation.

#### **Partition coefficient**

No information available.

### **12.4. Mobility in soil**

#### **Mobility**

The product is insoluble in water.

### **12.5. Results of PBT and vPvB assessment**

This product does not contain any substances classified as PBT or vPvB.

### **12.6. Other adverse effects**

None known.

---

## **SECTION 13: Disposal considerations**

---

### **13.1. Waste treatment methods**

#### **General information**

Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

#### **Disposal methods**

Dispose of waste product or used containers in accordance with local regulations

---

## **SECTION 14: Transport information**

---

<b>General</b>	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

### **14.1. UN number**

Not applicable.

### **14.2. UN proper shipping name**

Not applicable.

### **14.3. Transport hazard class(es)**

No transport warning sign required.

### **14.4. Packing group**

Not applicable.

### **14.5. Environmental hazards**

Environmentally hazardous substance/marine pollutant

No.

### **14.6. Special precautions for user**

Not applicable.

### **14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

---

## **SECTION 15: Regulatory information**

---

### **15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

## DMVB/CAMV

### EU legislation

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Dangerous Preparations Directive 1999/45/EC.

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

---

### SECTION 16: Other information

---

Revision date 18/09/2014

SDS number 4808

#### Hazard statements in full

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.