



Square Ceramic Surface Mount Medium Blow Fuse

HF 0678L Series-3912 Size

RoHS Compliant

Features

- Medium blow, Surface mount high current fuse
- Current rating from 10A to 30A
- Wide operating temperature range from -55°C to 125°C
- Tape & Reel for auto-insert SMD process
- Compatible with 260°C, IR Pb-free solder process
- RoHS compliant with exemption 7(a)
- Full compliance with EU Directive 2011/65/EU and amending directive 2015/863
- Halogen Free, (MSL=1)
- AEC-Q Compliant
- Meets Bel automotive qualification*
- * Largely based on internal AEC-Q test plan

Applications

- Voltage regulator module
- PC server
- Office electronic equipment
- Industrial equipment
- Medical equipment
- POE, POE+
- Power supply
- DC-DC converter

HALOGEN FREE = HF





Physical Specifications

| Materials | Body : Ceramic | |
|-----------|---|--|
| Materials | Terminations : Silver Plated Caps /Palladium Plated Caps | |
| | On Fuse : | |
| | "Current Rating", "L" – laser marked on ceramic tube, "bel" stamped in end caps. | |
| Marking | On Label : | |
| | "bel", "0678L", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and " .", " (China RoHS compliant). | |

Electrical Characteristics (UL/CSA STD.248-14) Safety Agency Approvals

| Tooting Current | Blow Time | | |
|-----------------|-----------|---------|--|
| Testing Current | Minimum | Maximum | |
| 100% | 4 hrs. | N/A | |
| 200% | N/A | 60 sec | |


| Safety Agency | Safety Agency Certificate | Ampere Rating/ Voltage Rating | Ampere Range / Volt @ I.R. ability* | | |
|---|------------------------------|----------------------------------|---|--|--|
| c 'RL ° us | E20624 | 10A-30A / 250V AC 72V DC | 10A-30A /250V @ 100A AC 125V @ 150A AC 72V @ 130A DC 65V @ 300A DC | | |
| *I.R.= Interrupting Rating = Short Circuit Rating(Amps) | | | | | |




Specifications subject to change without notice

Type 0678L

Temperature Derating Curve



Average Time Current Curve



Electrical Specifications

| Part Number | Ampere Rating | Nominal Cold Resistance (ohms) | Nominal Volt-drop @100%In (Volt) max. | Voltage and Interrupting Ratings | Melting I ² T @10 In (A ² Sec) Min. | Nominal Power Dissipation (W) | Agency Approvals |
|----------------|------------------|--------------------------------------|--|--|--|-------------------------------------|---------------------|
| 0678L9100-XX | 10A | 0.0056 | 0.18 | | 50 | 1.8 | Υ |
| 0678L9150-XX | 15A | 0.0036 | 0.12 | See Table of Safety Approvals on Page 1 for Voltage and associated Interrupting Ratings | 110 | 1.8 | Υ |
| 0678L9200-XX | 20A | 0.0025 | 0.09 | | 270 | 1.8 | Y |
| 0678L9250-XX | 25A | 0.0019 | 0.08 | | 420 | 2.0 | Y |
| 0678L9300-XX | 30A | 0.0013 | 0.07 | | 1000 | 2.1 | Y |

Consult manufacturer for other ratings

XX-Packaging code (see "ordering information")

NOTES:

Test Conditions

For all 0678L data, as well as UL Component investigation, all tests were conducted with fuse samples soldered on a PCB (1.6mm thick) test board with copper traces measuring 0.1mm nominal thickness (3 oz. clad), 10mm wide and 100mm overall length.

- UL Condition of Acceptability
- The following information is contained in the UL Component Recognition for 0678L Fuse Series:

The maximum temperature recorded in open air was 100°C in a 21°C ambient (79°C rise). Consideration should be given to checking operating temperatures in end-use application with regard to thermal index of surrounding materials and components.

(Maximum temperature recorded at 80% of rating (24A) for the 0678L 30 rating was 69°C (48°C rise).

Caution:

- Minimum fusing point:

The 0678L Series fuse are NOT intended to be operated at currents between 100% and 200% of ampere rating. Prolonged operation at currents in this range may result in overheating of the fuse and/or desoldering of the fuse caps from the PCB pad.



Specifications subject to change without notice

Bel Fuse Inc. 206 Van Vorst Street Jersey City, NJ 07302 USA +1 201.432.0463 Bel.US.CS@belf.com belfuse.com/circuit-protection Type 0678L


Environmental Specifications

| Shock Resistance | MIL-STD-202G, Method 213B, Test Condition 1 (100 G's peak for 6 milliseconds; Sawtooth waveform) | |
|----------------------------|--|--|
| Vibration Resistance | MIL-STD-202G, Method 201A (10-55 Hz, 0.06 inch, total excursion). | |
| Salt Spray Resistance | MIL-STD-202G, Method 101E, Test Condition B (48 hrs.). | |
| Insulation Resistance | MIL-STD-202G, Method 302, Test Condition A (After Opening) 10,000 ohms minimum. | |
| Solderability | MIL-STD-202G, Method 208H | |
| Resistance to solder Heat | MIL-STD-202G, Method 210F, Test Condition C. Top Side (260°C, 20 sec) MIL-STD-202G, Method 210F, Test Condition D. Bottom Side (260°C, 10 sec) | |
| Thermal Shock | MIL-STD-202G, Method 107G, Test Condition B (-65°C to +125°C). | |
| Operating Temperature | -55°C to +125°C | |
| Moisture Sensitivity Level | 1 (According to IPC J-Std-020) | |


| High temperature storage | MIL-STD-202 Method 108 | | |
|------------------------------|---|--|--|
| Temperature cycling | JESD22 Method JA-104,Test Condition B | | |
| Biased humidity | MIL-STD-202 Method 103, 85C/85% RH with 10% operating power for 1000 hrs. | | |
| Operational life | MIL-STD-202 Method 108, Test Condition D | | |
| Resistance to solvents | MIL-STD-202 Method 215 | | |
| Mechanical shock | MIL-STD-202 Method 213,Test Condition C | | |
| Vibration | MIL-STD-202 Method 204 | | |
| Resistance to soldering heat | MIL-STD-202 Method 210,Test condition B | | |
| Thermal shock | MIL-STD-202 Method 107 | | |
| Solderability | J-STD-002 | | |
| Board flex(SMD) | AEC-Q200-005 | | |
| Terminal strength | AEC-Q200-006 | | |
| Electrical characterization | 3 temperature electrical | | |

Soldering Parameters

| IR Reflow Profile (IPC/JEDEC J-STD-020D) | | | | |
|--|------------------|--|--|--|
| Preheat & Soak | | | | |
| Temperature min (T _{smin}) | 150℃ | | | |
| Temperature max (T _{smax}) | 200 ℃ | | | |
| Time (T _{smin} to T _{smax}) (t _s) | 60-120 seconds | | | |
| Average ramp-up rate(T _{smax} to T _p) | 3℃ / second max. | | | |
| Liquidous temperature(T _L) | 217℃ | | | |
| Time at liquidous (t _L) | 60 – 150 seconds | | | |
| Peak temperature (T _p) | 260℃ max | | | |
| Time (tp) within 5°C of the specified | 30 seconds | | | |
| classification temperature (T _c) | 30 Seconds | | | |
| Average ramp-down rate(Tp to Tsmax) | 6℃ / second max. | | | |
| Time 25°C to peak temperature | 8 minutes max. | | | |



| Lead-free Wave Soldering Profile | | |
|--|--|--|
| Wave Soldering Parameter | | |
| Average ramp-up rate | 200°C / second | |
| Heating rate during preheat | typical 1 - 2℃ / second Max 4℃ / second | |
| Final preheat temperature | within 125°C of soldering temperature | |
| Peak temperature Tp | 260℃ | |
| Time within +0 °C / -5 °C of actual peak temperature | 10 seconds | |
| Ramp-down rate | 5℃ / second max. | |



Specifications subject to change without notice




Bel Fuse Inc. 206 Van Vorst Street Jersey City, NJ 07302 USA +1 201.432.0463 Bel.US.CS@belf.com belfuse.com/circuit-protection Type 0678L

Fuse FGNO Explanation 0678L [XXXX] -XX


0678L=0678L Series; [XXXX]=Ampere Rating; XX=See Ordering Information as below

| Amps | Bel FGNO[XXXX] |
|------|----------------|
| 10 | 9100 |
| 15 | 9150 |
| 20 | 9200 |
| 25 | 9250 |
| 30 | 9300 |

Mechanical Dimensions



Ordering Information



Packaging

| Packaging Tape & Reel | Packaging Specification | Quantity | Quantity & Packaging Code |
|---|-------------------------|----------|---------------------------|
| 16mm wide tape with 13 inches Diameter reel | EIA Standard 481-E | 2000 | 2 |



Specifications subject to change without notice