

Thread former with internal cooling rad HSSE TiCN M ISO 2X (6HX) 0° 376

C

For universal use up to 1300 N/mm²

ATORN®

Application

For manufacturing metric threads in through and blind holes on CNC or conventional machines in the **steel, stainless steel and non-ferrous metals up to a strength of 1500 N/mm²**.



Advantage

- Innovative shape geometry optimised for machining high-strength materials
- High-quality, torsion-resistant HSSE cutting material and surface finish ensure a long service life

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.		
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC	
	28	12	10			30	40	30	40	25	35	30								

Art. no.	13395 840
Surface	TiCN
Lead angle shape	C
Thread type	Metric thread
Thread type x nominal diameter	M14
Pitch	2 mm
Cutting material	HSSE
Core hole diameter	13 mm
Length	110 mm
Hole type	Clearance/blind hole ≤ 3xD
Shaft diameter	11 mm
Shank square	9 mm
Coolant supply	Internal radial
Tolerance of screw taps	ISO 2X (6HX)
Application type/machine type	CNC, Conventional
Cutting speed (steel 1000) suitability	1
Cutting speed (steel 1300) suitability	1
Overall stainless steel suitability	3
fitness not iron total	2
Cutting speed (cast) suitability	3
fitness Titan/Nickel/Super total	3
Cutting speed (hard 65) suitability	3
DIN	376

EAN-Code

4050293438116