

SVQC steel boring bar, positive right
for longitudinal and copy turning using VC indexable inserts

ATORN®

Application

For longitudinal and copy turning with VC indexable insert 35°

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 107.5°, tip angle 35°, clearance angle 7°

Advantage

- very slim geometry, optimised for contour turning work
- positive body geometry ensures low cutting forces



Art. No.	17849 108
ISO name	A40T SVQC R/L 16
Min. bore diameter	49 mm
Shaft diameter	40 mm
Clearance length	40 mm
Length	300 mm
Clamping surface height	38 mm
Suitable for indexable inserts	VC.. 1604..
Tool design	Right

EAN-Code

4050293562446