

system trolley

for individual fitting

Application:

basic trolley can be individually equipped with various elements, e.g. as a cleaning trolley, 5S assembly trolley, tool/material provision trolley, for storage and mobile transport for slings or long, bulky tools, parts, cables etc.

Execution:

- sturdy sheet steel construction, fully welded
- outer walls and divider with 10x10 mm square perforations, grid spacing 38 mm, and slotted perforations for attaching support elements, hooks and various accessories
- mobile thanks to 4 steering rollers Ø 125 mm, with trackless light-grey solid rubber tread and thread protection, 2 rollers with wheel blocks
- easy to move with four integrated handles in outer walls
- ref. no. 110: centre divider – usable depth 300/300 mm
- ref. no. 112: asymmetrical divider – usable depth 400/200 mm
- additional colours (at no extra charge) and special equipment requirements deliverable on request

Advantage:

- THE UNIVERSAL TROLLEY with numerous equipment options – configure YOUR OWN individual trolley
- square and slotted perforations in walls enable the trolley to be custom-equipped as per requirements
- versatile and comprehensive accessories range for equipping trolley
- rapid retooling and conversion of accessories for changing workplace requirements



Art. no.	50240 302
Brand	HK
Manufacturer Part Number	50240302
Width	745 mm
Depth	650 mm
Height	1880 mm
Design	Divider centric
Load-carrying capacity	600 kg
Distance between centre of hole and centre of hole	38 mm
Number of steering rollers	4 PCS
Wheel diameter	125 mm
With wheel lock	Yes
Material	Sheet steel
Colour of trolley	Optional
Surface	Powder-coated
Gross Weight	44.000 kg
Product Group	559

EAN

4053625474455