


T120I

111-12219



T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties ensures a simple and quick installation. Whilst easily installed by hand, - manual and pneumatic (for high volume applications) tensioning tools are available to ensure consistency of installation.

For the routing, bundling and securing of cables, pipes and hoses.

Base Data**Application Method**

Quick, simple fixing by hand or with HellermannTyton tensioning tools

Colour

Natural (NA)

Package Content

100

Quantity (Sold Unit / EDP)

100

Quantity per

Bag

Recommended Application Tool

MK6, MK6PN, MK9, MK9HT, MK21, TWT2, MK9P

Logistic and Packaging**Carton Quantity**

2000

EAN code

4031026207742

Quantity of Europallet

36000

Weight (kg) (Metric)

3 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C

Specification

UL Listed

Product Dimensions**Bundle Diameter max (Imperial)**

3 "

Bundle Diameter max (Metric)

80

Bundle Diameter min (Imperial)

.188 "

Bundle Diameter min (Metric)

5

Cable Tie Head Length (imperial)

.393

Cable Tie Head Width (imperial)

.502

Cable Tie Width Max (imperial)

.300

Cable Tie Width max. (metric)

7.61

Length L (Imperial)

11.875 "

Length L (Metric)

300

Minimum Tensile Strength (imperial)

120

Minimum Tensile Strength (N)

535

Width W (Metric)

7.6

© HellermannTyton 2006