

# SIR-E Multi-Functional Electronic Sounder



RND 430-00052 (12/24V)



RND 430-00053 (120/240V)

Dispositivo di segnalazione acustica.

Acoustic warning device.  
Dispositif de signalisation acoustique.  
Akustisches Warngerät.  
Dispositivo de aviso acústico.

<b>CORPO</b> BODY CORPS KÖRPER CUERPO	PC										
<b>DIFFUSORE ACUSTICO</b> ACOUSTIC DIFFUSER DIFFUSEUR ACOUSTIQUE AKUSTISCHER DIFFUSOR DIFUSOR ACÚSTICO	PC										
<b>RESA ACUSTICA</b> SOUND OUTPUT RENDEMENT ACOUSTIQUE SOUND OUTPUT SALIDA DE SONIDO	Max = 100,0 dB(A) 1m										
<b>TENSIONE DI ALIMENTAZIONE</b> VOLTAGE TENSION SPANNUNG TENSIÓN	12/24 Vac/Vdc $\pm 10\%$ - 120/240 Vac $\pm 10\%$										
<b>SERVIZIO</b> SERVICE SERVICE BETRIEBSART FUNCIONAMIENTO	$\infty$										
<b>CORRENTE NOMINALE</b> CURRENT CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>12 Vaxdc</th> <th>24 Vac</th> <th>120 Vac</th> <th>240 Vac</th> </tr> </thead> <tbody> <tr> <td>mA</td> <td>230</td> <td>300</td> <td>40</td> <td>20</td> </tr> </tbody> </table>		12 Vaxdc	24 Vac	120 Vac	240 Vac	mA	230	300	40	20
	12 Vaxdc	24 Vac	120 Vac	240 Vac							
mA	230	300	40	20							
<b>EFFETTI SONORI</b> SOUND EFFETS ACOUSTIQUE SOUND EFECTOS DE SONIDO	N°16 suoni selezionabili tramite dip-switch n° 16 available sounds selectable by dip-switch n° 16 tonalités à selectioner par dip-switch Nr. 16 verfügbare Sounds per Dip-Schalter wählbar n° 16 sonidos disponibles seleccionables por dip-switch										
<b>GRADO IP</b> IP RATING DEGRE IP SCHUTZART GRADO IP	IP65										
<b>TEMPERATURA DI FUNZIONAMENTO</b> OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR TEMPERATURA DE FUNCIONAMIENTO	-40°C+55°C										
<b>VIBRAZIONI</b> VIBRATIONS VIBRATIONS VIBRATIONEN VIBRACIONES	INDUSTRIAL CEI 60068-2-6 SINE										

# SIR-E Multi-Functional Electronic Sounder



<b>CERTIFICAZIONI, OMOLOGAZIONI</b> <i>CERTIFICATIONS, APPROVALS CERTIFICAZIONI, HOMOLOGATIONS PRODUKTZERTIFIKATE, ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i>	CE, UKCA, EAC
<b>FISSAGGIO</b> <i>MOUNTING FIXATION FIXIERUNG FIJACIÓN</i>	<b>Viti su base</b> <i>Screws on the base Par vis sur la base Mit Schrauben am Sockel Tornillos en la base</i>
<b>DISEGNO</b> <i>TECHNICAL DRAWING DESSIN TECHNISCHE ZEICHNUNG DIBUJO TECNICO</i>	<p>The technical drawing consists of two views: a top view and a side view. The top view shows a circular base with a diameter of 52 mm. It features six mounting holes arranged in two rows of three. The distance between the centers of the two rows is 40 mm, and the distance from the center of the base to the center of each hole in a row is 20 mm. The diameter of each hole is 5 mm. The side view shows a cylindrical body with a total height of 102 mm and a base diameter of 92 mm. The top of the body is rounded. A speaker grille is visible on the front face, and a small circular hole is located on the front face near the bottom. The diameter of this hole is 20 mm.</p>