

# VOLTCRAFT

## DATASHEET

Item No.: 2533750

Type designation:

AG1/AG2/AG3/AG4/AG5/AG6/AG7/AG8/AG9/AG10/AG11/AG12/AG13

Chemical system: Zn/KOH-H<sub>2</sub>O/MnO<sub>2</sub>

Nominal voltage: 1.5 V

Weight: Approximate 0.34 g/ 0.5 g/ 0.7 g/ 0.4 g/ 1.0 g/ 0.6 g/ 0.75 g/ 0.9 g/ 1.0 g/ 1.1 g/ 0.4 g/ 1.6 g/ 2 g/

The dimensions shall be in accordance with the below figures both prior to and after the service output test.

Dimension (mm)

Designation	AG1	AG2	AG3	AG4	AG5
Diameter	6.50~6.80	7.55~7.90	7.55~7.90	6.60~6.80	7.55~7.90
Height	1.90~2.15	2.30~2.60	3.30~3.60	2.40~2.60	5.00~5.40
Designation	AG6	AG7	AG8	AG9	AG10
Diameter	9.25~9.50	9.15~9.50	11.25~11.60	9.25~9.50	11.25~11.60
Height	1.85~2.10	2.40~2.70	1.85~2.10	3.30~3.60	2.75~3.05
Designation	AG11	AG12	AG13		
Diameter	7.55~7.90	11.25~11.60	11.25~11.60		
Height	1.85~2.10	3.80~4.20	5.00~5.40		

Capacity:

Designation	AG1	AG2	AG3	AG4	AG5	AG6	AG7
Approximate Capacity (mAh)	6	14	35	12	40	16	22
Designation	AG8	AG9	AG10	AG11	AG12	AG13	
Approximate Capacity (mAh)	23	40	75	11	100	140	

Operating temperature: 10°C ~ 25°C

Recommend storage temperature: 20°C ± 2°C

Shelf lifetime: 3 Years

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.  
Copyright 2023 by Conrad Electronic SE.

2533750\_v1\_0623\_02\_voltcraft\_ds