



Torque Screwdrivers

TORQUE



NEW

MA500



Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	inch	Capacity Ncm		
MA500-1	112395	138.0	18.2	28.0	9.6	1/4	10 - 80	195	1
		5.43	0.72	1.10	0.38				
MA500-2	112401	157.0	18.2	28.0	9.6	1/4	40 - 200	260	1
		6.18	0.72	1.10	0.38				
MA500-3	112418	171.0	18.2	32.0	9.6	1/4	50 - 450	306	1
		6.73	0.72	1.26	0.38				

Store driver in the protective case at lowest torque setting.
Do not force adjusting knob below lowest setting.




NEW

MAL500



Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	inch	Capacity in. ozs./in. lbs		
MAL500-1	112593	138.0	18.2	28.0	9.6	1/4	20 - 100 in.ozs	195	1
		5.43	0.72	1.10	0.38				
MAL500-2	112609	157.0	18.2	28.0	9.6	1/4	3 - 15 in.lbs	260	1
		6.18	0.72	1.10	0.38				
MAL500-3	112616	171.0	18.2	32.0	9.6	1/4	5 - 40 in.lbs	306	1
		6.73	0.72	1.26	0.38				

Store driver in the protective case at lowest torque setting.
Do not force adjusting knob below lowest setting.



NEW

PS501



Product code	EAN code	A mm inch	B mm inch	C mm inch	D mm inch	inch	Capacity Ncm in. ozs./in. lbs		
PS501-1	0112425	115.0	18.2	28.0	9.6	1/4	4 - 22	147	1
		4.53	0.72	1.10	0.38		6 - 32 in.ozs		
PS501-2	0112432	141.0	18.2	28.0	9.6	1/4	7 - 70	187	1
		5.55	0.72	1.10	0.38		10 - 100 in.ozs		
PS501-3	0112449	141.0	18.2	28.0	9.6	1/4	15 - 170	198	1
		5.55	0.72	1.10	0.38		1.5 - 15 in.lbs		
PS501-4	0112456	154.0	18.2	32.0	9.6	1/4	45 - 450	270	1
		6.06	0.72	1.26	0.38		4 - 40 in.lbs		

