



Heat Shrinkable Tubing 3:1 on a Reel

HIS-A - with adhesive liner

HIS-A forms a seal against moisture and protect against corrosion and mechanical abrasion.

Features and Benefits

- Adhesive lined heat shrink tubing
- Inner wall melts when heated and is forced into gaps
- Adhesive forms seal against moisture as tubing cools
- Protects components
- Available in black and transparent
- 6 sizes for wide range of applications



HIS-A - with adhesive liner



Detailed Information about Heatguns please refer to page 529.

MATERIAL	Polyolefin, cross-linked (PO-X)
Shrink Ratio	3:1
Operating Temperature	-55 °C to +125 °C
Minimum Shrink Temperature	+100 °C
Longitudinal change after shrinkage	-10 % max.
Softening Point Adhesive	+85 °C
Dielectric Strength	15 kV/mm according to IEC 60684 P2
Flammability	UL224 VW-1 (except clear)
Insulation Class	A (VDE 0530)
Specifications	CSA, SAE - AMS - DTL-23053 / 4 , UL224 125 °C 600V VW-1



Heat Shrinkable Tubing 3:1 with adhesive

RoHS

TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Reel Length	Colour	Article-No.
HIS-A-3/1	3.0	1.0	1.00	10 m	Black (BK)	308-10300
	3.0	1.0	1.00	10 m	Transparent (CL)	308-10303
HIS-A-6/2	6.0	2.0	1.00	5 m	Black (BK)	308-10600
	6.0	2.0	1.00	5 m	Transparent (CL)	308-10603
HIS-A-9/3	9.0	3.0	1.40	5 m	Black (BK)	308-10900
	9.0	3.0	1.40	5 m	Transparent (CL)	308-10903
HIS-A-12/4	12.0	4.0	1.80	5 m	Black (BK)	308-11200
	12.0	4.0	1.80	5 m	Transparent (CL)	308-11203
HIS-A-18/6	18.0	6.0	2.25	4 m	Black (BK)	308-11800
	18.0	6.0	2.25	4 m	Transparent (CL)	308-11803
HIS-A-24/8	24.0	8.0	2.50	3 m	Black (BK)	308-12400
	24.0	8.0	2.50	3 m	Transparent (CL)	308-12403

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.