

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2033900323](#)
Status: **Active**
Overview: Quad-Row Board-to-Board Connectors
Description: Quad-Row Board-to-Board Plug, 0.175mm Pitch, 0.60mm Mated Height, 2.00mm Mated Width, 32 Circuits, 2 Reels/Carton

Documents:

Drawing (PDF)	Packaging Specification 2033909200-SPK-201 (PDF)
Product Specification 2033890000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2033890000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	PCB Headers
Series	203390
Application	Board-to-Board
Overview	Quad-Row Board-to-Board Connectors
Product Name	Quad-Row
Taxonomy	PCB Headers and Receptacles
UPC	196823168048

Physical

Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.60mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	5.570/mg
Number of Rows	4
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.175mm
Pitch - Termination Interface	0.175mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	2033890000-AS-000
Packaging Specification	2033909200-SPK-201
Product Specification	2033890000-PS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[203390 Series](#)

Mates With

Quad-Row Receptacle [203389](#)

This document was generated on 11/02/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION