# **Product Information Sheet**

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

#### Supplier's name or trade mark: Hera GmbH & Co KG

Supplier's address: FE, Dieselstraße 9, 32130 Enger Herford, DE

### Model identifier: LED Pipe F

## Type of light source:

The ball of the section of the secti			DIC
Lighting technology used:	LED	Non-directional or	DLS
		directional:	
Light source cap-type	nein		
(or other electric interface)			
Mains or non-mains:	NMLS	Connected light	Nein
		source (CLS):	
Colour-tuneable light source:	Nein	Envelope:	-
High luminance light source:	Nein		
Anti-glare shield:	Nein	Dimmable:	Only with
			specific dimmers


**Product parameters** 

#### Parameter Parameter Value Value General product parameters: Energy consumption in on-25 Energy efficiency G mode (kWh/1000 h), rounded class up to the nearest integer Useful luminous flux (duse), 1 331 in Wide Correlated colour 3 000 or 4 000 indicating if it refers to the flux cone (120°) temperature, in a sphere (360°), in a wide rounded to the cone (120º) or in a narrow cone nearest 100 Κ, (90º) or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set On-mode (P<sub>on</sub>), 22,3 Standby power (P<sub>sb</sub>), 0,00 power expressed in W expressed in W and rounded to the second decimal Networked standby power (P<sub>net</sub>) Colour rendering 95 index, rounded to for CLS. expressed in W and rounded to the second decimal the nearest integer, or the range of CRIvalues that can be set Outer Height 1 2 1 0 Spectral power See image dimensions distribution in the in last page 17 Width

without separate control gear, lighting control parts and non- lighting control parts,	Depth	17	range 250 nm to 800 nm, at full-load	
if any (millimetre) Claim of equivale	nt nower <sup>(a)</sup>		lf yes, equivalent	
claim of equivale	int power		power (W)	
			Chromaticity coordinates (x and y)	0,437 0,395
Parameters for d	irectional light s	ources:		
Peak luminous in	tensity (cd)	1	Beam angle in degrees, or the range of beam angles that can be set	120
Parameters for L	ED and OLED lig	ht sources:		
R9 colour renderi	ing index value	0	Survival factor	0,00
the lumen mainte	enance factor	0,00		
(a), , not applicable				

(a)<sub>'-'</sub> : not applicable;

(b)'-' : not applicable;



Wavelength(nm)