

## Drawer cabinet system 800 S with 11 drawers


Depth 800 mm, width 722 mm

### Execution:

- Load capacity of 70 kg with a drawer front height of 60 mm and 100 kg with a drawer front height of 90 mm
- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Drawers with perforated steel sheet base (25 mm hole spacing) for attaching and fixing individual items
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- Load capacity of 100 kg with a drawer front height of 90 mm

### Advantage:

- Optimum operating characteristics of drawers
- High quality - made in Germany



<b>Art. no.</b>	<b>50310 120</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50310120
<b>Number of drawers</b>	11 PCS
<b>Height</b>	1568 mm
<b>Width</b>	722 mm
<b>Depth</b>	800 mm
<b>Height x width x depth</b>	1568 x 722 x 800 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	600 x 700 mm
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	Yes
<b>Load-carrying capacity per drawer</b>	200 kg
<b>Drawer surface</b>	0.42 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>With SOFT-CLOSE closing function</b>	No
<b>With single pull-out safety brake</b>	Yes
<b>Central locking</b>	Yes
<b>Material of cover panel</b>	Wood, plastic-coated
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Surface</b>	Powder-coated
<b>Functions</b>	RFID possible
<b>Model</b>	S8 49/11
<b>Overall surface</b>	4.62 m <sup>2</sup>
<b>Lock type</b>	DOM® locking system
<b>Material</b>	Sheet steel
<b>Gross Weight</b>	252.000 kg
<b>Product Group</b>	5BB

### EAN

4039247462643