

Features

- ◆ Wide 2 : 1 input range
- ◆ Input filter to meet EN 55022, Class A and FCC, level A without external components
- ◆ Extended operating temperature range -40°C to 85°C
- ◆ I/O isolation 1'500 VDC
- ◆ DIP-24 package
- ◆ High reliability, MTBF >1.0 Mio. h
- ◆ 3-year product warranty



The TEN 3N Series is a drop in replacement of the prevalent TEN 3 Series. The up-to-date design enables a cost reduction without any compromise to reliability and function. They come with an internal filter to meet EN55022 class A without external components. Increased EMC immunity and extended operating temperature range of -40°C to 85°C make these converters an ideal solution for cost critical but demanding applications. With the standard pinning it is a drop in replacement for common 3 Watt converters in DIP24 package.

Models				
Ordercode	Input voltage range	Output voltage	Output current max.	Efficiency typ.
TEN 3-0510N	4.5 – 9.0 VDC (nominal 5 VDC)	3.3 VDC	600 mA	77 %
TEN 3-0511N		5.0 VDC	500 mA	78 %
TEN 3-0512N		12 VDC	250 mA	82 %
TEN 3-0513N		15 VDC	200 mA	82 %
TEN 3-0515N		24 VDC	125 mA	81 %
TEN 3-0521N		±5.0 VDC	±250 mA	77 %
TEN 3-0522N		±12 VDC	±125 mA	81 %
TEN 3-0523N		±15 VDC	±100 mA	81 %
TEN 3-1210N	9 – 18 VDC (nominal 12 VDC)	3.3 VDC	600 mA	79 %
TEN 3-1211N		5.0 VDC	500 mA	81 %
TEN 3-1212N		12 VDC	250 mA	85 %
TEN 3-1213N		15 VDC	200 mA	85 %
TEN 3-1215N		24 VDC	125 mA	84 %
TEN 3-1221N		±5.0 VDC	±250 mA	80 %
TEN 3-1222N		±12 VDC	±125 mA	84 %
TEN 3-1223N		±15 VDC	±100 mA	84 %
TEN 3-2410N	18 – 36 VDC (nominal 24 VDC)	3.3 VDC	600 mA	79 %
TEN 3-2411N		5.0 VDC	500 mA	81 %
TEN 3-2412N		12 VDC	250 mA	85 %
TEN 3-2413N		15 VDC	200 mA	85 %
TEN 3-2415N		24 VDC	125 mA	84 %
TEN 3-2421N		±5.0 VDC	±250 mA	80 %
TEN 3-2422N		±12 VDC	±125 mA	84 %
TEN 3-2423N		±15 VDC	±100 mA	84 %
TEN 3-4810N	36 – 72 VDC (nominal 48 VDC)	3.3 VDC	600 mA	79 %
TEN 3-4811N		5.0 VDC	500 mA	81 %
TEN 3-4812N		12 VDC	250 mA	85 %
TEN 3-4813N		15 VDC	200 mA	85 %
TEN 3-4815N		24 VDC	125 mA	84 %
TEN 3-4821N		±5.0 VDC	±250 mA	80 %
TEN 3-4822N		±12 VDC	±125 mA	84 %
TEN 3-4823N		±15 VDC	±100 mA	84 %

Input Specifications

Input current no load	5 Vin models	65 mA typ.
	12 Vin models	35 mA typ.
	24 Vin models	20 mA typ.
	48 Vin models	15 mA typ.
Start-up voltage	5 Vin models:	4.5 VDC (or lower)
	12 Vin models:	9 VDC (or lower)
	24 Vin models:	18 VDC (or lower)
	48 Vin models:	36 VDC (or lower)
Under voltage shut down (lock-out circuit)	5 Vin models:	4.0 VDC max.
	12 Vin models:	8.5 VDC max.
	24 Vin models:	17.5 VDC max.
	48 Vin models:	35.5 VDC max.
Surge voltage (1 sec. max.)	5 Vin models	11 V max.
	12 Vin models	25 V max.
	24 Vin models	50 V max.
	48 Vin models	100 V max.
Reflected ripple current	5 Vin models	100 mA typ
	12 Vin models	30 mA typ.
	24 Vin models	15 mA typ.
	48 Vin models	10 mA typ.
Conducted noise	EN 55022 class A without external components	
ESD (electrostatic discharge)	EN 61000-4-2, air ± 8 kV, contact ± 6 kV, perf. criteria A	
Radiated immunity	EN 61000-4-3, 10 V/m, perf. criteria A	
Fast transient / surge (with external input capacitor)	EN 61000-4-4, ± 2 kV, perf. criteria A	
	EN 61000-4-5, ± 1 kV perf. criteria A Nippon chemi-con KY 220 μ F, 100 V, ESR 48 mOhm – external input capacitor	
Conducted immunity	EN 61000-4-6, 10 Vrms, perf. criteria A	
Short circuit input power	2000 mW max.	
Internal power dissipation	1200 mW max.	

Output Specifications

Voltage set accuracy	± 2 % max.	
Regulation	– Input variation Vin min. to Vin max.	1.0 % max.
	– Load variation 0 – 100 %	
	single output models	1.0 % max.
	dual output models balanced load	2.0 % max.
Minimum load	not required	
Ripple and noise (20 MHz bandwidth)	70 mVpk-pk max	
Transient response time (25% load step change)	500 μ s max.	
Transient response deviation (25% load step change)	± 5 % max.	
Temperature coefficient	± 0.02 %/K	
Current limitation	>120 % of Iout max., constant current	
Short circuit protection	continuous	

Output Specifications (continued)

Capacitive load	3.3 VDC models:	680 μ F max.
	5.0 VDC models:	470 μ F max.
	12 VDC models:	330 μ F max.
	15 VDC models:	220 μ F max.
	24 VDC models:	100 μ F max.
	\pm 5.0 VDC models:	220 μ F max. (each output)
	\pm 12 VDC models:	150 μ F max. (each output)
	\pm 15 VDC models:	100 μ F max. (each output)

General Specifications

Temperature ranges	- Operating (natural convection cooling 20 LFM)	-40°C to +85°C
	- Case temperature	+100°C max.
	- Storage	-55°C to +125°C
Derating		3.3 %/K above 70°C
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MTTF (MIL-HDBK217 F, @ +25°C, ground benign)		>1 Mio. h
Isolation voltage (60 sec.)	- Input/Output	1'500 VDC
Isolation capacitance	- Input/Output	300 pF max.
Isolation resistance	- Input/Output (500 VDC)	>1'000 M Ohm
Switching frequency		90 kHz min. (pulse frequency modulation PFM)
Safety standards		cUL/UL 60950-1, IEC/EN 60950-1
Safety approval		CSA file no. 226037 http://directories.csa-international.org
Environmental compliance	- Reach	www.tracopower.com/products/reach-declaration.pdf
	- RoHS	RoHS directive 2011/65/EU


Application note: www.tracopower.com/products/ten3n-application.pdf

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Physical Specifications

Casing material	non conductive FR4
Potting material	epoxy (UL 94V-0 rated)
Pin material	copper alloy with gold plated subplate
Weight	12.8 g (0.45 oz)
Soldering temperature	max. 260°C / 10 sec.

Outline Dimensions



Dimensions in [mm], () = Inch
 Pin diameter $\varnothing 0.5 \pm 0.05$ (0.02 \pm 0.002)
 Tolerances ± 0.5 (± 0.02)
 Pin pitch tolerances ± 0.25 (± 0.01)

Pin-Out		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	ntc	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

ntc = not to connect