

HEATERS CSL 030 CLIP FASTENING 250 W, AC 230 V



Figure similar

| Model | | |
|--|------|--------------------------|
| product brand name | | SIVACON |
| Product designation | | semiconductor fan heater |
| General technical data | | |
| Active power consumption / Rated value | W | 400 |
| Operating temperature / minimum | °C | -45 |
| Volume flow rate / free-blowing | m³/h | 45 |
| Voltage | | |
| Inrush current / typical | A | 9 |
| Protection class | | |
| Protection class IP | | IP20 |
| Main circuit | | |
| Operating voltage | | |
| • with AC / at 50 Hz / Rated value / maximum | V | 230 |
| • with AC / at 60 Hz / Rated value / minimum | V | 230 |
| • with AC / at 60 Hz / Rated value / maximum | V | 230 |
| Operating current / of the slow-blow fuse link | A | 6.3 |
| Product details | | |
| Product component | | |
| • blower | | Yes |
| • Thermostat | | No |
| Connections | | |

| | | |
|---|-----|-----|
| Tightening torque / with screw-type terminals / maximum | N·m | 0.8 |
|---|-----|-----|

Mechanical Design

| | | |
|-----------------------------|----|---------|
| Height | mm | 90 |
| Width | mm | 85 |
| Depth | mm | 111 |
| Material / of the enclosure | | plastic |

Environmental conditions

| | | |
|----------------------------|----|-----|
| Ambient temperature | | |
| • during storage / minimum | °C | -45 |
| • during storage / maximum | °C | 70 |

Certificates

| | | |
|--------------------------|--|---|
| Equipment marking | | |
| • acc. to DIN EN 61346-2 | | R |
| • acc. to DIN EN 81346-2 | | E |

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21505A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21505A/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21505A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



8MR2150-A_ALL

last modified:

11.03.2015