



Description

- Oven controlled crystal oscillator (OCXO) with voltage control on a FR4 base with a metal lid.

| | |
|----------------------|------------|
| ■ Model | IQOV-162-3 |
| ■ Model Issue number | 2 |

Frequency Parameters

- Frequency: 19.20MHz
- Frequency Tolerance @ 25°C: ±500.00ppb
- Frequency Stability: ±20.00ppb
- Operating Temperature Range: -40.00 to 85.00°C
- Ageing: ±5ppb max per day, ±500ppb max per year
- Supply Voltage Variation (measurement referenced to frequency observed with TA=25°C, Vs varied from 3.13V to 3.47V, VC =1.65V and load=15pF): ±10ppb max
- Ageing: Vs, VC, TA constant measurement referenced to frequency observed with TA=25°C, Vs= 3.3V, VC=1.65V and after 30 days of operation.
- Load Variation (5% load change measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC =1.65V and load=15pF): ±10ppb max
- Short Term Stability - Allan Variance (temperature stability, no EMI/EMC or other interference test after power for 1hr ref. to 25°C; 1s, using PN9000 equipment): 0.1ppb max / 1sec
- Frequency Tolerance (measurement referenced to frequency observed with TA=25°C, Vs=3.3V, VC=1.65V and after 15 minutes of operation, within 30 days after ex-works): ±500ppb
- Frequency Stability: TA varied from -40°C to 85°C, measurement referenced to frequency observed with $f_{ref} = (f_{max} + f_{min}) / 2$, Vs=3.3V, VC=1.65V, load=15pF, temperature variable speed less than 2°C per minute.

Electrical Parameters


- Supply Voltage: 3.3V
- Supply Voltage Tolerance: ±5%
- Current Draw:
Warm up: 560mA max
Steady state (@ 25°C): 250mA max
- Warm-Up Time (@ 25°C, F<±100ppb of final frequency): 5mins max

Frequency Adjustment


- Pulling: ±3ppm to ±8ppm
- Control Voltage Details: 1.65V ±1.65V
- Linearity: ±10% max
- Slope: Positive
- Input Impedance: 100kΩ min

Output Details

- Output Compatibility: HCMOS
- Output Load: 15pF
- Rise and Fall time: 8ns max
- Duty Cycle: 45/55%
- Output Low (@ Vs=3.3V, load=15pF): 0.4V max
Output High (@ Vs=3.3V, load=15pF): 2.4V min



Outline (mm)



Sales Office Contact Details:

UK: +44 (0)1460 270200

France: +33 (0)5 34 50 91 18

Email: info@iqdfrequencyproducts.com

Germany: +49 (0)7264 9145-62

USA: +1 408.273.4530

Web: www.iqdfrequencyproducts.com



Noise Parameters

- Phase Noise (@ 10MHz typ):
 - 100dBc/Hz @ 10Hz
 - 130dBc/Hz @ 100Hz
 - 145dBc/Hz @ 1kHz
 - 150dBc/Hz @ 10kHz
 - 150dBc/Hz @ 100kHz
 - 155dBc/Hz @ 1MHz

Environmental Parameters

- Shock: IEC 60068-2-27, Test Ea, Severity 50A: 50G, 11ms duration, 1/2 sine wave, 3 times in each of 3 mutually perpendicular planes
- Vibration: IEC 60068-2-06, Test Fc: 10Hz-500Hz, 0.75mm displacement, 10G acceleration, one cycle per 30mins, 3 times in each of 3 mutually perpendicular planes, test 2hrs
- Storage Temperature Range: -55 to 105°C
- Operable Temperature Range: -40 to 85°C
- ESD Level:
 - HBM, Class 2: 2000V to 4000V, JEDEC JS-001-2010
 - Machine Model, Class B: 200V to 400V, JEDEC JS-001-2010

Manufacturing Details

- Maximum Reflow Temperature: 260°C (30secs max)
- Moisture Sensitivity Level: 2

Compliance

- RoHS Status Compliant
- REACH Status Compliant

Packaging

- Pack Type: Bulk Loose in bulk pack
- Pack Size 1
- Alternative packing option available

This document is correct at the time of printing; please contact your local office for the latest version.

Sales Office Contact Details:

UK: +44 (0)1460 270200

France: +33 (0)5 34 50 91 18

Email: info@iqdfrequencyproducts.com

Germany: +49 (0)7264 9145-62

USA: +1 408.273.4530

Web: www.iqdfrequencyproducts.com