

## Product information

# 13 96 200 T

## Pliers for Electrical Installation

IEC 60900 DIN EN 60900



- 6 functions in one pair of pliers
- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping wire ferrules
- Pliers with integrated, insulated tether attachment point for a tool tether
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the gripping surfaces for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 - 1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>
- Crimping die for wire ferrules 0.5 - 2.5 mm<sup>2</sup>
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm<sup>2</sup> / Ø 15 mm
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened



| General         |                                                                                                                      |
|-----------------|----------------------------------------------------------------------------------------------------------------------|
| Article No.     | 13 96 200 T                                                                                                          |
| EAN             | 4003773081425                                                                                                        |
| Pliers          | chrome-plated                                                                                                        |
| Head            | chrome-plated                                                                                                        |
| Handles         | insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether |
| Weight          | 280 g                                                                                                                |
| Dimensions      | 200 x 63 x 28 mm                                                                                                     |
| Standard        | DIN EN 60900 IEC 60900                                                                                               |
| REACH compliant | does not contain SVHC                                                                                                |
| RoHS compliant  | not applicable                                                                                                       |

| Technical details                                |                                                  |
|--------------------------------------------------|--------------------------------------------------|
| Cutting capacity copper cable, multiple-stranded | Ø 15 mm                                          |
| Cutting capacity copper cable, multiple-stranded | 50 mm <sup>2</sup>                               |
| Stripping capacity for cross-sections            | 0.75 — 1.5 mm <sup>2</sup> / 2.5 mm <sup>2</sup> |
| Capacity in square millimetres                   | 0.5 — 2.5 mm <sup>2</sup>                        |
| AWG                                              | 1 / 0                                            |
| Drop Protection System                           | yes                                              |
| VDE tested                                       | yes                                              |

technical change and errors excepted

